







LABEL

FAIRVIEW MICROWAVE FM2CP1126-10 D/C: YYWW

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.





C	1126-10	FM2CP1126-10	K.DANG	R5	3F	⊳
REV		ITEM NO.	DRAWN BY		CAGE CODE	SIZE
N/A	SCALE N	NCE ONLY.	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.	ENSIONS SHO	ALL DIM	
H	SHEET 1	120 [3048] < L ≤ 300 [7620] = +6 [152] / -0 300 [7620] < L = +5%L / -0	120 [3048] < L ≤ 300 300 [76	() ()		300
RTY OF CORPO	DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION ALL RIGHT'S RESERVED.	L ≤ 12 [305] = +1 [25] / -0 12 [305] < L ≤ 60 [1524] = +2 [51] / -0 60 [1524] < L ≤ 120 [3048] = +4 [102] / -0	12 [305] < L ≤ 60 60 [1524] < L ≤ 120	FRACTIONS ± 1/32 ANGI ES + 1°	$X = \pm .2$ [5.08] $XX = \pm .02$ [.51] $XXX = \pm .005$ [.13]	× × ×
ON A	THE INFORMATION AND	(L) TOLERANCES:	CABLE LENGTH (L) TOLERANCES	NCES:	TOLERANCES	
	THIRD-ANGLE PROJECTION	ONS ARE INCHES	UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS	WISE SPECIF	ESS OTHER	S