







## LABE

FAIRVIEW MICROWAVE FM2CP1126-20 D/C: YYWW

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS

NGLE PROJECTION

CABLE LENGTH (L) TOLERANCES:



TITLE

		an INFINIT® brand
ALL DIMENSIONS	.X = ±.2 [5.06] FRACH .XX = ±.02 [.51] ± 1/3 .XXX = ±.005[.13] ANGLE	TOLERANCES:

FRACTIONS ± 1/32 ANGLES ± 1°

L ≤ 12 [305] = +1 [25] / -0
12 [305] < L ≤ 60 [1624] = +2 [51] / -0
60 [1524] < L ≤ 120 [3048] = +4 [102] / -0
120 [3048] < L ≤ 300 [7620] = +6 [182] / -0
300 [7620] < L = +5%L / -0

THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICHOWAVE CORPORATION.
ALL RIGHTS RESERVED.