



Fairview Microwave THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS.

an INFINIT® brand A X=±.2 [5.08] FRACTIONS XX=±.02 [.51] ±1/32 XXX=±.005[.13] ANGLES±1° CAGE CODE 3FKR5 ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY. TOLERANCES: DRAWN BY ITEM NO. MVEERAPPAN L ≤ 12 [305] = +1 [25] / -0
12 [305] < L ≤ 60 [1624] = +2 [51] / -0
60 [1524] < L ≤ 120 [3048] = +4 [102] / -0
120 [3048] < L ≤ 300 [7620] = +6 [182] / -0
300 [7620] < L = +5%L / -0 CABLE LENGTH (L) TOLERANCES:

FMAD1224

N/A

REV

THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICKOWAVE CORPORATION.
ALL RIGHTS RESERVED.

III III III