

1/4 -36UNS-2A 3.5mm FEMALE .84 [21.3] 2.4mm FEMALE M7X0.75P

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS.

an INFINIT® brand Fairview Microwave

TITLE

A SIZE X=±.2 [5.08] FRACTIONS XX=±.02 [.51] ±1/32 XXX=±.005[.13] ANGLES±1° CAGE CODE 3FKR5 ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY. DRAWN BY ITEM NO. L ≤ 12 [305] = +1 [25] / -0
12 [305] < L ≤ 60 [1624] = +2 [51] / -0
60 [1524] < L ≤ 120 [3048] = +4 [102] / -0
120 [3048] < L ≤ 300 [7620] = +6 [182] / -0
300 [7620] < L = +5%L / -0 CABLE LENGTH (L) TOLERANCES: FMAD1261 THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICKOWAVE CORPORATION.
ALL RIGHTS RESERVED.

N/A

REV