

DETAIL A

HYBRID, D-SUB 7-PIN MALE		
PIN #	DESCRIPTION	SPECIFICATIONS
A1	VDD	28 VDC
A2	GND	Ground
1	ENABLE	Amplifier Enable: TTL Logic High (3.3V) (Internally Pulled-Low)
2	CURRENT SENSE	Analog voltage relative to IDD@ 100mV per Ampere
3	TEMP SENSE	Analog voltage relative to Module's Temperature @ 10 mV/°C
4	NC	No electrical connection
5	GND	Ground

**Fairview Microwave**  
an INFINIT@ brand  
FMAM5061  
S/N: XXXXXXXX


LABEL

STANDARD TOLERANCES

.X	±0.2
.XX	±0.01
.XXX	±0.005

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

- NOTES:
- ADEQUATE HEATSINK REQUIRED.



**Fairview Microwave**  
an INFINIT@ brand

TITLE

NOTES:  
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
3. DIMENSIONS ARE IN INCHES [mm].

DWG NO	FMAM5061	CAGE CODE	3FKR5
CAD FILE	SHEET 1 OF 1	SCALE	N/A
		SIZE	A
			7361