

D-SUB 9-PIN, MALE		SPECIFICATIONS	
PIN #	DESCRIPTION		
1	N/C	No electrical connection	
2	ALARM	Amplifier Alarm Indicator: Normally TTL Low	
3	SHUTDOWN	Amplifier Disable: TTL Logic High (3.3V) (Internally Pulled-Low)	
4	TEMP SENSE	Analog voltage relative to Module's Temperature @ 10 mV/°C	
5	CURRENT MONITOR	Analog voltage relative to IDD @ 100mV per Ampere	
6,7	VDD	28 VDC	
8,9	GND	Ground	


LABEL



STANDARD TOLERANCES
 .X ±0.2
 .XX ±0.01
 .XXX ±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

- NOTES:
- ADEQUATE HEATSINK REQUIRED.



TITLE

NOTES:
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
 3. DIMENSIONS ARE IN INCHES [mm].

DWG NO		CAGE CODE	
FMAM5064		3FKR5	
CAD FILE	07/30/19	SHEET	1 OF 1
SCALE N/A		SIZE	A
			7361