



8.5

=1110

5.9 [150]

4.7 [120]

NOTES:

1. LABEL PER ILS-100-03 (FOR INTERNAL REFERENCE ONLY)
LABEL LOCATION FOR REFERENCE ONLY

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT

ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

IN IERS OTHERWISE SEPCIFIED LEADING DIVERSIONS ARE INCHES



TITLE an INFINIT® brand

A O		$ \begin{array}{c ccccccccccccccccccccccccccccccccccc$			ONLE
CAGE CODE	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.			TOLERANCES:	——————————————————————————————————————
Z) Si				NCES:	DIMENSIONS
K.GLEBOVA				CABLE LENGTH (L) TOLERANCES:	ONLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES
ITEM NO. FMANI				L) TOLERANCES:	ONG ARE INCHES
FMANLP1009	SCALE N	SHEET 1 C	DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION ALL RIGHTS RESERVED.	THE INFORMATION AND	
A REV	N/A	<u>1</u>	OCUMENT RTY OF CORPORATION. SERVED.	ON AND	/ j\ 8