

2.2-5 FEMALE

N MALE

## NOTES:

- CABLES 84" AND UNDER HAVE 1 LABEL CENTERED. CABLES OVER 84" HAVE 2 LABELS, ONE AT EACH END 12.0" FROM THE END OF THE CONNECTOR. 6" FROM CABLE END 1 PLACE FOR ALL LENGTHS OF CABLE.

Ņ

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



an INFINIT® brand

TITLE

SIZE		X=±.2 [5.08] FRACTIONS XX=±.02 [.51] ±1.02 XXX=±.005[.13] ANGLES±1°			DIMENSIONS IN [] ARE MILLIMETERS	
CAGE CODE	ALL DIN			TOLER		
	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.	FRACTIONS ± 1/32 ANGLES ± 1°		TOLERANCES:		
DRAWN BY		L ≤ 12 [305] = +1 [25] / 0 12 [305] < L ≤ 60 [4524] = +2 [51] / 0 60 [1524] < L ≤ 720 [3048] = +4 [102] / 0 120 [3048] < L ≤ 300 [7620] = +6 [152] / 0 300 [7620] < L = +5%L / -0		CABLE LENGTH (L) TOLERANCES:		
ITEM NO.		L ≤ 300 [7620] = +6 [152] / -0 300 [7620] < L = +5%L / -0	L ≤ 12 [305] = +1 [25] / -0 12 [305] < L ≤ 60 [1524] = +2 [51] / -0 [1524] < L ≤ 120 [3048] = +4 [102] / -0	_) TOLERANCES:	20 AND   10 CHIEF OF	
	SCALE N	SHEET 1	DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION ALL RIGHTS RESERVED.	<b>→</b>		
REV	N/A	OF 1	DOCUMENT RTY OF CORPORATION. SERVED.	THE INFORMATION AND	4	

⊳

3FKR5

MVEERAPPAN

FMCA2375