

6

5


4

3


2

1

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	09/11/2023	KGLEBOVA	AAFKHAMI



RECOMMENDED  
PCB LAYOUT  
FOR REFERENCE ONLY



UNLESS OTHERWISE SPECIFIED  
LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS

**TOLERANCES:**

X = $\pm .2$ [5]	FRACTIONS
.XX = $\pm .02$ [0.5]	$\pm 1/32$
.XXX = $\pm .005$ [0.13]	ANGLES $\pm 1^\circ$

**CABLE LENGTH TOLERANCES:**

$\leq 12$ [305]	$\leq 60$ [1524]	$\leq 120$ [3048]	$\leq 300$ [7620]	$\leq 3000$ [76200]
$\pm .01$ [0.25]	$\pm .01$ [0.25]	$\pm .01$ [0.25]	$\pm .01$ [0.25]	$\pm .01$ [0.25]

ALL DIMENSIONS ARE FOR REFERENCE ONLY  
AND SUBJECT TO CHANGE WITHOUT NOTICE.  
UN-DIMENSIONED/NON-CRITICAL FEATURES  
MAY VARY IN SIZE AND LOCATION  
COLORS MAY VARY



Website: [www.FairviewMicrowave.com](http://www.FairviewMicrowave.com)  
Phone: 1.800.715.4396 | 1.972.649.6678

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
SCALE	SHEET
NONE	1 OF 1

DESCRIPTION  
**2.4 mm JACK SOLDERLESS PCB MOUNT 2 HOLE FLANGE TEMP RATED 85 DEG C 50 GHz VSWR1.5**

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	3FKR5	KGLEBOVA	FMCN45937	A

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

6

5

4

3

2

1