





LABEL:

FAIRVIEW MICROWAVE FMIR1031 D/C: XXXX

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

Fairview Microwave

JITLE

	ß		×			
>	SIZE C		.XXX = ±.005 [.13]	.X=±.2 [5.08		UNLES
3F	CAGE CODE	ALL DIME		[5.08] [2 [.51]	TOLERANCES	S OTHER
3FKR5		ENSIONS SHC	FRACTIONS ± 1/32 ANGLES ± 1°		NCES:	VISE SPECIFI
DFRISIELLO	DRAWN BY	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.	120 [3048] < L ≤ 300 [7620] = +6 [152] / -0 300 [7620] = +6 [152] / -0 300 [7620] < L = +5%L / -0	$L \le 12 [305] = +1 [25] / -0$ $12 [305] < L \le 60 [1524] = +2 [51] / -0$	CABLE LENGTH (L) TOLERANCES	UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES
FMIR1031	ITEM NO.	NCE ONLY.	20 [3048] < L ≤ 300 [7620] = +6 [152] / -0 300 [7620] < L = +5%L / -0	L) TOLERANCES:	NS ARE INCHES	
1031		SCALE N	ALL RIGHTS RESERVED SHEET OF	THE INFORMATION AND	THIRD-ANGLE PROJECTION	
≻	REV	N/A	OF 1	DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION.	ION AND	