



LABEL:

FAIRVIEW MICROWAVE  
FMIR1037  
D/C: XXXX

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS, DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



TITLE

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [ ] ARE MILLIMETERS				THIRD-ANGLE PROJECTION	
TOLERANCES:				THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED.	
FRACTIONS		CABLE LENGTH (L) TOLERANCES:		SCALE	
.X = ±.2	[.508]	L ≤ 12 [305]	= +1 [25] / -0	N/A	
.XX = ±.02	[.51]	12 [305] < L ≤ 60 [1524]	= +2 [51] / -0	REV A	
.XXX = ±.005	[.13]	60 [1524] < L ≤ 120 [3048]	= +4 [102] / -0		
ANGLES ± 1°		120 [3048] < L ≤ 300 [7620]	= +6 [152] / -0		
		300 [7620] < L	= +5% / -0		
SIZE	GAGE CODE	DRAWN BY	ITEM NO.	SCALE	
A	3FKRS	DFRISIELLO	FMIR1037	N/A	
ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.					