




REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	04/08/22	DREBECK



TNC PLUG
REVERSE POLARITY



TNC JACK
REVERSE POLARITY

- NOTES:
1. SEE LABEL SPECIFICATION ILS-100.
FOR INTERNAL REFERENCE ONLY.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS, DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



TITLE

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES				THIRD-ANGLE PROJECTION	
DIMENSIONS IN [] ARE MILLIMETERS				 THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED.	
TOLERANCES:		CABLE LENGTH (L) TOLERANCES:		SHEET 1 OF 1	
X = ±.2 [5.08]	FRACTIONS ± 1/32	L ≤ 12 [305]	= +1 [25] / -0	SCALE N/A	
XX = ±.02 [.51]	± 1/32	12 [305] < L ≤ 60 [1524]	= +.2 [5.1] / -0	REV A	
XXX = ±.005 [.13]	ANGLES ± 1°	60 [1524] < L ≤ 120 [3048]	= +.4 [10.2] / -0	DRAWN BY DFRISIELLO	
		120 [3048] < L ≤ 300 [7620]	= +.6 [15.2] / -0	ITEM NO. FMSP1072	
		300 [7620] < L = +5%/L / -0		GAGE CODE 3FKRS	
ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.				SIZE A	
GAGE CODE 3FKRS		DRAWN BY DFRISIELLO		REV A	