



THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES

Fairview Microwave

an INFINIT® brand

Þ	SIZE	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY	.X = ±.2 .XX = ±.02 .XXX = ±.02		DIMENSIONS IN 11 ARE MILLIMETERS TOLERANCES: CABLE LENGTH (L) TOLERANCES:	
34	CAGE CODE		.X=±.2 [5.08] .XX=±.02 [.51] (XX=±.005[.13]	TOLER		
3FKR5			.X=±.2 [5.08] FRACTIONS .XX=±.02 [.51] ±1/32 .XXX=±.005[.13] ANGLES±1°	ANCES:		
DFRISIELLO	DRAWN BY	WN ARE FOR REFEREI	12 [305] < L = 60 [1524] = 42 [31] - 0 60 [1524] < L = 120 [3048] = +4 [102] / -0 120 [3048] < L = 300 [7620] = +6 [152] - 0 300 [7620] < L = +5%L / -0	CABLE LENGTH (
FMTR1103	ITEM NO.	NCE ONLY.	12 [305] < L ≤ 80 [1524] = +2 [51] +0 60 [1524] < L ≤ 120 [3048] = +4 [102] /-0 20 [3048] < L ≤ 300 [7620] = +6 [152] /-0 300 [7620] < L = +5%L /-0	GTH (L) TOLERANCES:		
		SCALE	FAIRVIEW M ALL SHEET	THE		
		N/A	IS THE PROPERTY OF W MICROWAVE CORPOL ALL RIGHTS RESERVED OF	THE INFORMATION AND DESIGN IN THIS DOCUMENT	₽ ↓	
Α	REV	Ά	IS THE PROPERTY OF FARVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED. SHEET OF 1 1	ON AND	4	