



NOTES:

FLANGE DETAIL

LABEL PER ILS-100-09. FOR INTERNAL USE ONLY.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED. UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS





A | CAGE CODE 3FKR5 ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY. DRAWN BY
K.DANG FMW229TR1001 REV

CABLE LENGTH (L) TOLERANCES:

12 (305) = +1 (25) / 0

12 (305) < 1 < 60 (1924) = +2 (51) / 0

12 (305) < 1 < 60 (1924) = +2 (51) / 0

12 (3048) < 1 < 300 (7820) = +6 (192) / 0

120 (3048) < 1 < 300 (7820) < 1 = +5%L / -0

300 (7820) < 1 = +5%L / -0

300 (7820) < 1 = +5%L / -0

SCALE

WN ARE FOR REFERENCE ONLY.

DRAWN BY

| ITEM NO. | | REV

NGLE PROJECTION

 $X = \pm .2$ [5.08] $XX = \pm .02$ [.51] $XXX = \pm .005$ [.13]

FRACTIONS ± 1/32 ANGLES ± 1° TOLERANCES:

T-Rev.D