



WR-10 WAVEGUIDE  
W/UG387/U-M FLANGE  
2 PLS

0.12 [3.04] DIA THRU  
C-BORE 0.1875 [4.7625] DIA x 0.13 [3.30] DP  
4 PLS

0.100 [2.540] X 0.075 [1.905]  
O-RING GROOVE

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN: Inches [mm]  
TOLERANCES ARE:  
DECIMALS ±0.01 FRACTIONS ± 1/64  
.XX ±.01 ANGLES ±1/2°  
.XXX ±.005 FRACTIONS ± 127/320  
[±.127]

NOTE:  
O-RING INSIDE DIAMETER: 0.750" [19.050]  
O-RING WIDTH: 3/32" [2.38]

\* THESE DIMENSIONS AND TOLERANCES SUPERSEDE NOTE # 1 ON TITLE BLOCK.

# FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE		DWG NO		CAGE CODE	
		FMWAD5000		3FKR5	
NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].		CAD FILE	SHEET	SCALE	SIZE
		052416		N/A	A
					2233