



0.1722Ø
[4.4] THRU
(8 HOLES)

| CPR-90G Dimension | Inches | mm |
|-------------------|--------|-------|
| A | 1.156 | 29.36 |
| B | 0.891 | 22.63 |
| C | 0.578 | 14.68 |
| D | 0.266 | 6.76 |
| E | 0.400 | 10.16 |
| F | 0.906 | 23.01 |
| G | 1.590 | 40.39 |
| H | 2.090 | 53.09 |
| I | 1.124 | 28.55 |
| J | 0.900 | 22.86 |
| K | 0.516 | 13.11 |
| L | 0.828 | 21.03 |
| M | 1.141 | 28.98 |
| N | 1.656 | 42.06 |

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES.
DECIMALS .X ±.030
.XX ±.015
.XXX ±.005
ANGLES ±1/2 DEG.
FRACTIONS ±1/32

* THESE DIMENSIONS AND TOLERANCES
SUPERSEDE NOTE #1 ON TITLE BLOCK.

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

TITLE

DWG NO

FMWCA1007

CAGE CODE

3FKR5

CAD FILE

092116

SHEET

SCALE N/A

SIZE A

2233