




REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	1/28/2020	J GARCIA



Label:

PN: SA3N10W-40
SN: XXXXXXXXX
BIDIRECTIONAL ATTENUATOR
3GHz M/F 10 Watts 40dB



THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS, DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.					SCALE	
SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV	N/A	
A	3FKR5	K.DANG	SA3N10W-40	A		

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES		THIRD ANGLE PROJECTION	
DIMENSIONS IN [] ARE MILLIMETERS			
TOLERANCES:		THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED.	
CABLE LENGTH (L) TOLERANCES:		SHEET 1 OF 1	
L ≤ 12 [305] = +1 [25] / -0			
12 [305] < L ≤ 60 [1524] = +2 [51] / -0			
60 [1524] < L ≤ 120 [3048] = +4 [102] / -0			
120 [3048] < L ≤ 300 [7620] = +6 [152] / -0			
300 [7620] < L = +5%L / -0			

X = ±.2 [5.08] FRACTIONS			
XX = ±.02 [.51] ± 1/32			
XXX = ±.005 [.13] ANGLES ± 1°			