









THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S., LAW PROHIBITED.



an INFINIT® brand

TITLE

⊳	SIZE		X=±.2 [5.08] FRACTIONS XX=±.02 [.51] ± 1/32 XXX=±.005[.13] ANGLES±1		< +		CNL
<u>ې</u>	CAGE CODE	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY			TOLERANCES:	ESS OTHER	
3FKR5	E					DIMENSIO	
	DR.		L ≤ 12 [305] < L 1 [25] / 0 45 12 [305] < L ≤ 60 [1524] = +2 [51] / .0 60 [1524] < L ≤ 120 [3048] = +4 [102] / .0 300 [7620] < L = +5%L / .0 300 [7620] < L = +5%L / .0		CABLE LENGTH	NS IN [
K.DANG	DRAWN BY	NARE FOR REFERE				UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS	
SC5342	PART NUMBER	ENCE ONLY.			2 [305] = +1 [25] / -0	CABLE LENGTH (L) TOLERANCES:	ONS ARE INCHES
		SCALE N	SHEET 1 C				THIRD-ANGLE PROJECTION
⊳	REV	N/A)F 1				/i\ OECTION