


.030±.002 [0.76±0.05] SLOT



THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

Fairview Microwave

■ an INFINIT® brand

⊳	SIZE		) 	X	<     +			ON
3F	CAGE CODE	ALL DIMENSIONS SHO	X=±.2 [5.08] FRACTIONS XX=±.02 [.51] ±1/32 XXX=±.005[.13] ANGLES±1°			TOLERANCES:		יטט כוחבד
3FKR5						NCES:		DIMENSIONS
K.DANG	DRAWN BY	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.	120 [3048] < L ≤ 300 300 [76;	60 [1524] < L ≤ 120 [3048] = +4 [102] / -0	CABLE LENGTH (L) TOLERANCES		DIMENSIONS IN [] ARE MILLIMETERS	
SC5504	ITEM NO.	NCE ONLY.	120 [3048] < L ≤ 300 [7620] = +6 [152] / -0 300 [7620] < L = +5%L / -0	L ≤ 12 [305] = +1 [25] / -0	L) TOLERANCES:		ONO ARE INCHES	
504		SCALE N	SHEET 1	DESIGN IN THIS DOCUMENT	THE INFORMATION AND	4		
Þ	REV	N/A	OF <b>1</b>	FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED.	RTYOF	ION AND	4	7