




WR42 Dimension	Inches	mm
A	0.640	16.26
H	0.875	22.23
J	0.670	17.02
K (± 0.002)	0.420	10.67
L (± 0.002)	0.170	4.32
AA	0.155	3.94
AB	4.025	102.24
AC	1.56	42.41
AD	2.13	54.10



BACK VIEW



STANDARD TOLERANCES
 .X ± 0.2
 .XX ± 0.1
 .XXX ± 0.05

*STANDARD TOLERANCES APPLY
 ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC.
 ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

NOTES:
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
 3. DIMENSIONS ARE IN INCHES [mm].

TITLE		DWG NO		CAGE CODE	
		SH142-20		3FKR5	
CAD FILE	120916	SHEET		SCALE	N/A
		SIZE	A		41742