



WR62	Inches	mm
Dimension		
A	0.994	25.25
H	1.313	33.35
J	0.956	24.28
K (± 0.002)	0.622	15.80
L (± 0.002)	0.311	7.90
AA	0.180	4.57
AB	1.000	25.40
AC	0.820	20.83
AD	1.160	29.46



BACK VIEW

STANDARD TOLERANCES

.X ± 0.2
 .XX ± 0.1
 .XXX ± 0.05

*STANDARD TOLERANCES APPLY
 ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

NOTES:
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
 3. DIMENSIONS ARE IN INCHES [mm].

TITLE		DWG NO		CAGE CODE	
		SH162-10		3FKR5	
CAD FILE	120916	SHEET		SCALE	N/A
				SIZE	A
					41742