



BNC FEMALE

MCX PLUG

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

ONLY



JITE

SIZE CAG	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.	.X=±.2 [5.08] .XX=±.02 [.51] .XXX=±.005 [.13]	<u> 10</u>
CAGE CODE   [		.X=±.2 [5.08] FRACTIONS .XX=±.02 [.51] ±1/32 .XXX=±.005[.13] ANGLES±1°	DIMENSIONS II
DFRISIELLO		L ≤ 12 [305] = +1 [25] / 0 12 [305] < L ≤ 90 [1624] = +2 [51] / 0 60 [1524] < L ≤ 120 [3048] = +6 [102] / 0 120 [3048] < L ≤ 300 [7620] = +6 [152] / 0 300 [7620] < L = +5%L / 0	DIMENSIONS IN [] ARE MILLIMETERS  NCES: CABLE LENGTH (L) TOLERANCES
ITEM NO. SM3665			) TOLERANCES:
	SCALE N/A	DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MISCAWAVE CORPORATION ALL RIGHTS RESERVED.  SHEET  OF  1  1  OF  1	<b>4</b>
A REV	Ά	OCUMENT OCUMENT RIY OF CORPORATION. SERVED. F	