





NOTES:

LABEL PER ILS-100-05. FOR INTERNAL USE ONLY.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS, DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

| INJURY STATES OF THE BADING DESCRIPTION APENDING SERVICES OF THE BADING DIVERSION APENDED.



>	SIZE	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.	X=±.2 [5.08] FRACTIONS XX=±.02 [.51] ±1/32 XXX=±.005[.13] ANGLES±1°					ONL
3F	CVCE CODE					TOLERANCES:	I SS CIHE	
20			FRACTIONS ± 1/32 ANGLES ± 1°		0	NOES.	DIMENSIONS IN [] ARE MILLIMETERS	WISE STECT
K.DANG	DBAWN BY		120 [3048] < L ≤ 300 300 [762			CABLE LENGTH (L) TOLERANCES:		ED LEADING DIMENSIC
ITEM NO. SMW/28HC001-10	ITEM NO		L ≤ 12 [305] = +1 [25] / -0 12 [305] < L ≤ 60 [1524] = +2 [51] / -0 60 [1524] < L ≤ 120 [3048] < L ≤ 120 [7620] = +6 [152] / -0 120 [3048] < L ≤ 300 [7620] < L = +5%L / -0 300 [7620] < L = +5%L / -0			1) TOI FRANCES:	ONG ARE INCHES	
	סה//	SCALE N/A	SHEET OF 1	DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED.	THE INFORMATION AND		\$	THIS CHANGER TROUBLE TOW