

Lead Free 1553 TRB 2-Slot Plug to Blunt Cut Genderless Cable 78 Ohm FMBC-30-02001 Coax in 36 Inch with Bend Relief

The 78 ohm TRB 2-Slot plug to 78 ohm Blunt cut genderless 36 inch cable using 78 ohm FMBC-30-02001 twinax, part number FM3MSA00571-36, from Fairview Microwave is in-stock and ships same day. This Fairview TRB 2-Slot to Blunt Cut cable assembly has a plug to genderless gender configuration with 78 ohm flexible FMBC-30-02001 twinax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FM3MSA00571-36 TRB 2-Slot plug to Blunt cut genderless cable assembly operates to 400 MHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		400	MHz
Capacitance		19.7 [64.63]		pF/ft [pF/m]
Operating Voltage (AC)			1,000	Vrms

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Length*	36 in [914.4 mm]
Weight	0.196 lbs [88.9 g]

Cable

Cable Type	FMBC-30-02001
Impedance	78 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PE
Shield Layer 1	Silver Plated Copper
Jacket Material	PVC, Blue

One Time Minimum Bend Radius	2.42 in [61.47 mm]
------------------------------	--------------------



Configuration:

- TRB 2-Slot Plug
- Blunt Cut Genderless
- FMBC-30-02001

Features:

- Max Frequency 400 MHz
- PVC Jacket
- MIL-STD-1553
- -20°C to +75°C
- 78 ohms

Applications:

- General Purpose
- Laboratory Use
- MIL-STD-1553
- Data

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Connectors

Description	Connector 1	Connector 2
Type	TRB 2-Slot Plug BayonetBlunt Cut Genderless Other	
Option	Bend Relief Spring	
Impedance	78 Ohms	78 Ohms
Contact Material & Plating	Bronze, Gold 30 micro inches	
Contact Plating Spec.	ASTM-B-488	
Dielectric Type	Teflon	
Outer Cond Material & Plating	Phosphor Bronze, Gold	
Outer Cond Plating Spec.	30 micro inches	
Body Material & Plating	Brass, Nickel	
Body Plating Spec.	ASTM-B-733	

Environmental Specifications
Temperature

Operating Range -20 to +75 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration: **FM3MSA00571 - xx uu**

cm = Centimeters
<blank> = Inches
Length


Example: FM3MSA00571-12 = 12 inches long cable
FM3MSA00571-100cm = 100 cm long cable

Lead Free 1553 TRB 2-Slot Plug to Blunt Cut Genderless Cable 78 Ohm FMBC-30-02001 Coax in 36 Inch with Bend Relief from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [Lead Free 1553 TRB 2-Slot Plug to Blunt Cut Genderless Cable 78 Ohm FMBC-30-02001 Coax in 36 Inch with Bend Relief FM3MSA00571-36](#)

URL: <https://www.fairviewmicrowave.com/lead-free-1553-trb-2-slot-plug-to-blunt-cut-genderless-cable-78-ohm-fmbc-30-02001-coax-in-36-inch-with-bend-relief-fm3msa00571-36-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



LEAD FREE SOLDER

LENGTH

LABEL
SEE NOTE 1 & 2


WWW.FAIRVIEWMICROWAVE.COM
FMXXXXXXXXXXXX

78 OHM TWINAX CABLE
JACKET: PVC, BLUE
NOM: DIA: .242" [6.15]

TRB 2-SLOT PLUG

TRB 3-SLOT PLUG

BEND RELIEF



NOTES:

1. CABLE ASSY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROX CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROX 6 INCHES FROM EACH CONNECTOR.
2. CABLE ASSEMBLY LENGTH DETERMINED BY ILLUSTRATED: FM3MSA00571-XX (-XX = OAL IN INCHES)
3. CABLES ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE IN INCHES DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:	FRACTIONS
.X = ±.2 [5]	.XX = ±.02 [0.5]
.XX = ±.005 [0.13]	ANGLES ± 1°
CABLE LENGTH TOLERANCES:	
≤ 12 [305]	±.1 [25]
> 12 [305] ≤ 60 [1524]	±.2 [51]
> 60 [1524] ≤ 300 [7620]	±.3 [7.62]
> 300 [7620]	±.5 [12.7]
> 120 [3048]	±.300 [7620]
	±.5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE UNLESS OTHERWISE SPECIFIED. DIMENSIONS MAY VARY COLORS MAY VARY

<p>Fairview Microwave an INFINIT[®] brand</p>		<p>INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5</p>
<p>Website: www.FairviewMicrowave.com</p> <p>Phone: 1.800.715.4396 1.972.649.6678</p>	<p>SCALE: NONE</p> <p>SHEET: 1 OF 1</p>	
<p>DESCRIPTION: Lead Free 2-Slot TRB Plug to Bend Relief 3-Slot TRB Plug 1553 Twinax Cable Using 78 Ohm FMBC-30-02001</p>		
<p>SIZE: A</p> <p>CAGE CODE: 3FKR5</p>	<p>DRAWN BY: KDANG</p>	<p>ITEM NO.: FM3MSA00571</p> <p>REV: A</p>