

LSZH 1553 TRB 2-Slot Plug to Blunt Cut Sexless Cable 78 Ohm TWCH-78-2 Coax in 24 Inch

The 78 ohm TRB 2-Slot plug to Blunt cut sexless 24 inch cable using 78 ohm TWCH-78-2 twinax, part number FM3MSA00604-24, from Fairview Microwave is in-stock and ships same day. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FM3MSA00604-24 TRB 2-Slot plug to Blunt cut cable assembly operates to 500 MHz. The FM3MSA00604 cable assembly consists of a 78 Ohm Low Smoke Zero Halogen TRB 2-Slot Solder/Clamp Plug with Blunt Cut for TWCH-78-2 cable (.242 O.D.) suitable for MIL-STD-1553 Applications. The zero halogen jacket cable reduces the amount of toxic and corrosive gases emitted during combustion. Typically used in poorly ventilated areas, zero halogen is very popular with military contractors and anywhere the protection of people and equipment from toxic and corrosive gases is critical.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Description | Min | Typ | Max | Units |
|------------------------|-----|--------------|-------|--------------|
| Frequency Range | DC | | 500 | MHz |
| Capacitance | | 21.2 [69.55] | | pF/ft [pF/m] |
| Operating Voltage (AC) | | | 1,000 | Vrms |

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

| | |
|---------|----------------------|
| Length* | 24 in [609.6 mm] |
| Weight | 0.297 lbs [134.72 g] |

Cable

| | |
|--------------------------------------|----------------------|
| Cable Type | TWCH-78-2 |
| Impedance | 78 Ohms |
| Inner Conductor Type | Stranded |
| Inner Conductor Material and Plating | Copper, Silver |
| Dielectric Type | PE |
| Shield Layer 1 | Silver Plated Copper |
| Jacket Material | HF POF, Blue |

| | |
|------------------------------|--------------------|
| One Time Minimum Bend Radius | 1.25 in [31.75 mm] |
|------------------------------|--------------------|



Configuration:

- TRB 2-Slot Plug
- Blunt Cut
- TWCH-78-2

Features:

- Max Frequency 500 MHz
- HF POF Jacket
- MIL-STD-1553
- -30°C to +80°C
- 78 ohms
- Low Smoke Zero Halogen
- Non-Toxic

Applications:

- General Purpose
- Laboratory Use
- Military Contractors
- MIL-STD-1553
- Data
- Safer Environments
- Ventilation critical areas
- Hospitals

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Connectors

| Description | Connector 1 | Connector 2 |
|-------------------------------|------------------------------|-----------------|
| Type | TRB 2-Slot Plug Bayonet | Blunt Cut Other |
| Impedance | 78 Ohms | |
| Contact Material & Plating | Bronze, Gold 30 micro inches | |
| Contact Plating Spec. | ASTM-B-488 | |
| Dielectric Type | Teflon | |
| Outer Cond Material & Plating | Phosphor Bronze, Gold | |
| Outer Cond Plating Spec. | 30 micro inches | |
| Body Material & Plating | Brass, Nickel | |
| Body Plating Spec. | ASTM-B-733 | |

Environmental Specifications
Temperature

Operating Range -30 to +80 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration: **FM3MSA00604 - xx uu**

cm = Centimeters
<blank> = Inches

Length

Example: FM3MSA00604-12 = 12 inches long cable
FM3MSA00604-100cm = 100 cm long cable

LSZH 1553 TRB 2-Slot Plug to Blunt Cut Sexless Cable 78 Ohm TWCH-78-2 Coax in 24 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [LSZH 1553 TRB 2-Slot Plug to Blunt Cut Sexless Cable 78 Ohm TWCH-78-2 Coax in 24 Inch FM3MSA00604-24](#)

URL: <https://www.fairviewmicrowave.com/lszh-1553-trb-2-slot-plug-to-blunt-cut-sexless-cable-78-ohm-twch-78-2-coax-in-24-inch-fm3msa00604-24-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

