

## Bend Relief TRB 3-Lug Jack Insulated Bulkhead to Blunt Cut 1553 Cable 48" Using 124 Ohm TWC-124-2 Twinax

The 78 ohm TRB 3-Lug jack bulkhead insulated to Blunt cut genderless 48 cable using 124 ohm TWC-124-2 twinax, part number FM3MSA00667-48, from Fairview Microwave is in-stock and ships same day. This Fairview TRB 3-Lug to Blunt Cut cable assembly has a jack to genderless gender configuration with 124 ohm flexible TWC-124-2 twinax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FM3MSA00667-48 TRB 3-Lug jack to Blunt cut genderless cable assembly operates to 500 MHz. Our RF cable assembly with TRB 3-Lug bulkhead insulated interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		500	MHz
Capacitance		12.3 [40.35]		pF/ft [pF/m]
Operating Voltage (AC)			1,000	Vrms

### Mechanical Specifications

#### Cable Assembly

Length*	48 in [121.92 cm]
Weight	0.266 lbs [120.66 g]

#### Cable

Cable Type	TWC-124-2
Impedance	124 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PE
Shield Layer 1	Silver Plated Copper
Jacket Material	PVC, Blue

One Time Minimum Bend Radius	1.25 in [31.75 mm]
------------------------------	--------------------



### Configuration:

- TRB 3-Lug Jack Bulkhead Insulated
- Blunt Cut Genderless
- TWC-124-2

### Features:

- Max Frequency 500 MHz
- PVC Jacket
- 124 ohms
- Twinaxial
- MIL-STD-1553B
- -40°C to +80°C
- Lead Free Solder
- Standard and Custom Lengths Available

### Applications:

- General Purpose
- Laboratory Use
- MIL-STD-1553B Applications
- Data Transmission

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

**Connectors**

Description	Connector 1	Connector 2
Type	TRB 3-Lug Jack Bayonet	Blunt Cut Genderless Other
Option	Bend Relief Spring	
Mount Method	Bulkhead Insulated	
Specification	MIL-STD-1553	
Impedance	78 Ohms	
Contact Material & Plating	Bronze, Gold 30 micro inches	
Contact Plating Spec.	ASTM-B-488	
Dielectric Type	Teflon	
Outer Cond Material & Plating	Phosphor Bronze, Gold	
Outer Cond Plating Spec.	30 micro inches	
Body Material & Plating	Brass, Nickel	
Body Plating Spec.	ASTM-B-733	

**Environmental Specifications**

**Temperature**

Operating Range -40 to +80 deg C

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

**How to Order**

Part Number Configuration:

**FM3MSA00667 - xx uu**

cm = Centimeters  
<blank> = Inches  
Length

Example: FM3MSA00667-12 = 12 inches long cable  
FM3MSA00667-100cm = 100 cm long cable

Bend Relief TRB 3-Lug Jack Insulated Bulkhead to Blunt Cut 1553 Cable 48" Using 124 Ohm TWC-124-2 Twinax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [Bend Relief TRB 3-Lug Jack Insulated Bulkhead to Blunt Cut 1553 Cable 48" Using 124 Ohm TWC-124-2 Twinax FM3MSA00667-48](https://www.fairviewmicrowave.com/1553-trb-3-lug-jack-bulkhead-insulated-to-blunt-cut-genderless-cable-124-ohm-twc-124-2-coax-in-48-bend-relief-spring-fm3msa00667-48-p.aspx)

URL: <https://www.fairviewmicrowave.com/1553-trb-3-lug-jack-bulkhead-insulated-to-blunt-cut-genderless-cable-124-ohm-twc-124-2-coax-in-48-bend-relief-spring-fm3msa00667-48-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



