

## NOTES:


MATERIAL:


MAIN BODY AND DUST CAP: PBT + GF, UL94V-0
HOOD: MOLDED 25P PVC
ADAPTER:
BODY: COPPER, NICKEL PLATING
INSULATOR: WHITE PLASTIC STEEL
CONTACT: COPPER, GOLD PLATING

PHYSICAL CHARACTERISTICS:
OPERATING TEMPERATURE RANGE: -10°C TO +60°C.
STORAGE TEMPERATURE RANGE: -40°C TO +68°C.
HUMIDITY: 10% ~ 90% RH
IP RATING: IP68-WHEN DUST CAP IS ENGAGED.

**ELECTRICAL:**IMPEDANCE: 75 OHM

PACKAGING:
ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN
ACCORDANCE WITH L-COM SPECIFICATION PS-0031.





RECOMMENDED PANEL OPENING

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



an INFINIT® brand

TITLE

