

N Male to BNC Male Cable LMR-400-UF Coax

Electrical Specifications

Frequency Range	DC to 3 GHz
Impedance	50 Ohms
Velocity of Propagation	85 %
RF Shielding	90 dB

Mechanical Specifications

Temperature

Temperature Operating Range	-40 to +85 deg C
-----------------------------	------------------

Size

Diameter	0.8125 in [20.64 mm]
Cable Color	Black

Cable

Description	Cable
Cable Type	LMR-400-UF
Inner Conductor Type	Stranded
Cable Inner Conductor	Copper
No of Shields	1
Dielectric Type	PE (F)
Jacket Material	PE
Jacket Diameter	0.405 in [10.29 mm]

Connectors

Description	Connector 1	Connector 2
Type	N Male	BNC Male
Configuration	Straight	Straight
Inner Conductor Material & Plating	Brass, Gold	Brass, Nickel
Inner Conductor Plating Spec.	50µ" Minimum	
Outer Conductor Material & Plating	Brass, Tri-Metal	Brass, Nickel
Coupling Nut Material & Plating		Brass, Nickel
Hex Size	13/16 inch	
Body Material & Plating	Brass, Tri-Metal	Brass, Nickel
Dielectric Type	Teflon	Teflon

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

Notes:

- Values at +25 °C, sea level
- BNC Male to N Male Cables




Configuration:

- N Male
- BNC Male
- LMR-400-UF

Fairview Microwave
 1130 Junction Dr. #100
 Allen, TX 75013
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Typical Performance Data



How to Order

Part Number Configuration:

FMC0108405 - xx uu

cm = Centimeters
 <blank> = Inches
 Length


Example: FMC0108405-12 = 12 inches long cable
 FMC0108405-100cm = 100 cm long cable

N Male to BNC Male Cable LMR-400-UF Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [N Male to BNC Male Cable LMR-400-UF Coax FMC0108405-XX](#)

URL: <http://www.fairviewmicrowave.com/n-male-bnc-male-cable-times-lmr-400-ultraflex-coax-fmc0108405-xx-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE N Male to BNC Male Cable LMR-400-UF Coax		DWG NO FMC0108405-XX		CAGE CODE 3FKR5	
CAD FILE	101614	SHEET	SCALE	N/A	SIZE A 5568