

SMA FLEXIBLE CABLES 6 GHZ LMR240

FMC0220240-XX

SPECIFICATIONS


CABLE ASSEMBLY:
 VSWR: <1.2 dB TYPICAL @ 6 GHZ

RAW CABLE:
 LOSS (EXCLUDING CONNECTORS)
 @ 1GHZ: 0.08 DB/FT
 @ 2GHZ: 0.38 DB/FT
 @ 3GHZ: 0.47 DB/FT


OUTER DIAMETER: 0.240"

CONNECTORS:
 SMA: NICKEL PLATED BRASS
 CONTACTS: Au PLATING 30μ-in
 INTERFACE: MIL-STD-348A

TORQUE WRENCH: 5 IN-IBS



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA FLEXIBLE CABLES 6 GHZ LMR240

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	FMC0220240-XX	--
SCALE	SHEET		