

# FMC0208058 DATA SHEET

### SMA Male to BNC Male Cable RG-58 Coax

### **Electrical Specifications**

Min	Тур	Max	Units	
DC		1,000	MHz	
		1.35:1		
	66		%	
30	30.8 [101.05]		pF/ft [pF/m]	
	DC	DC 66	DC 1,000 1.35:1 66	

### **Mechanical Specifications**

**Cable Assembly** 

 Diameter
 0.571 in [14.5 mm]

 Weight
 0.00838 lbs [3.8 g]

Cable

Cable Type
Cable Type
RG-58
Impedance
Inner Conductor Type
Inner Conductor Material and Plating
Dielectric Type
Number of Shields
RG-58
50 Ohms
Copper, Tin
PE
1

Shield Layer 1 Jacket Material Jacket Diameter Tinned Copper Braid PVC, Black 0.195 in [4.95 mm]

### **Connectors**

Description	Connector 1	Connector 2	
Туре	SMA Male	BNC Male	
Configuration	Straight	Straight	
Polarity	Standard	Standard	
Impedance	50 Ohms	50 Ohms	
Contact Material & Plating	Brass, Gold	Brass, Gold	
Contact Plating Spec.	50µ in. minimum	30µ in. minimum	
Dielectric Type	PTFE	PTFE	
Hex Size	5/16 inch		
Torque	4 in-lbs [0.45 Nm]		
Body Material & Plating	Brass, Gold	Brass, Nickel	
Body Plating Spec.	3µ in. minimum	100µ in. minimum	

### **Environmental Specifications**

**Temperature** 

Operating Range -65 to +165 deg C

**Compliance Certifications** (see product page for current document)

### **Plotted and Other Data**

Notes:

# dew Wicrose

## **Configuration:**

- SMA Male
- BNC Male
- RG-58

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com



FMC0208058-12 = 12 inches long cable


FMC0208058-100cm = 100 cm long cable



Length

### **Typical Performance Data**

Example:



SMA Male to BNC Male Cable RG-58 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: SMA Male to BNC Male Cable RG-58 Coax FMC0208058

URL: https://www.fairviewmicrowave.com/sma-male-bnc-male-cable-rg58cu-coax-fmc0208058-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
SMA Male to BNC Male Cable RG-58 Coax	DWG NO FMC0208058-XX			CAGE CODE 3FKR5		
	CAD FILE 101514	SHEET	SCALE	N/A	SIZE A	5568