

FMC0210315LF DATA SHEET

SMA Male to 10-32 Male Cable RG-316 Coax with LF Solder

The SMA male to 10-32 male cable using RG-316 coax, part number FMC0210315LF, from Fairview Microwave is in-stock and ships same day. This Fairview SMA to 10-32 cable assembly has a male to male gender configuration with 50 ohm flexible RG-316 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC0210315LF SMA male to 10-32 male cable assembly operates to 1 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Ty	/p Ma	ax Units
Frequency Range	DC		1,0	00 MHz
VSWR			1.3	5:1
Velocity of Propagation		70		%
Capacitance		32 [104.99]		pF/ft [pF/m]

Mechanical Specifications

Cable Assembly

Length*

0 in [0 mm]

Cable

Cable Type Impedance Inner Conductor Type

Inner Conductor Material and Plating

Dielectric Type Number of Shields Shield Layer 1 Jacket Material

Jacket Material Jacket Diameter RG-316

50 Ohms Solid

Copper, Silver

PTFE

1

Silver Plated Copper Braid

FEP, Tan

0.098 in [2.49 mm]



Configuration:

- SMA Male
- 10-32 Male
- RG-316

Features:

- Max Frequency 1 GHz
- 70% Phase Velocity
- FEP Jacket

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com

sales@fairviewmicrowave.com





Connectors

Description Connector 1		Connector 2			
Туре	SMA Male	10-32 Male			
Impedance	50 Ohms	50 Ohms			
Contact Material & Plating	Brass, Gold	Brass, Gold			
Contact Plating Spec.	50μ in. minimum	MIL-G-45204			
Dielectric Type	PTFE	PTFE			
Body Material & Plating	Brass, Nickel	Brass, Nickel			
Body Plating Spec.	100μ in. minimum				
Hex Size	5/16 inch				
Torque	4 in-lbs 0.45 Nm				

Environmental Specifications

Temperature

Operating Range

-65 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

FMC0210315LF - xx uu

cm = Centimeters

chlank> = Inches

Length

Example: FMC0210315LF-12 = 12 inches long cable
FMC0210315LF-100cm = 100 cm long cable

SMA Male to 10-32 Male Cable RG-316 Coax with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: SMA Male to 10-32 Male Cable RG-316 Coax with LF Solder FMC0210315LF


URL: https://www.fairviewmicrowave.com/standard-sma-male-10-32-male-cable-rg316-coax-fmc0210315lf-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
SMA Male to 10-32 Male Cable RG-316 Coax with LF Solder	DWG NO FMC0210315LF			CAGE CODE 3FKR5			
	CAD FILE 101514	SHEET	SCALE	N/A	SIZE A	5568	