

FMC0228315 DATA SHEET

SMA Male to RA SMC Plug Cable RG-316 Coax

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		3	GHz
VSWR			1.35:1	
Velocity of Propagation		70		%
Capacitance	3	32 [104.99]	pF/ft [pF/m]

Mechanical Specifications

Cable Assembly Diameter

Weight

Cable

Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Shield Layer 1 Jacket Material Jacket Diameter

0.01544 lbs [7 g] RG-316 50 Ohms Stranded Copper, Silver PTFE

0.551 in [14 mm]

PTFE 1 Silver Plated Copper Braid FEP, Tan 0.098 in [2.49 mm]

Connectors

Description	Connector 1	Connector 2		
Туре	SMA Male	SMC Plug		
Configuration	Straight	Right Angle		
Polarity	Standard	Standard		
Impedance	50 Ohms	50 Ohms		
Contact Material & Plating	Brass, Gold	Beryllium Copper, Gol		
Contact Plating Spec.	50µ in. minimum	50µ in. minimum		
Dielectric Type	PTFE	PTFE		
Hex Size	5/16 inch	1/4 inch		
Torque	4 in-lbs [0.45 Nm]			
Body Material & Plating	Brass, Nickel	Brass, Gold		
Body Plating Spec.	100µ in. minimum	3µ in. minimum		

Environmental Specifications

Temperature Operating Range

-65 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:



Configuration:


- SMA Male
- SMC Plug Right Angle
- RG-316

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Typical Performance Data



SMA Male to RA SMC Plug Cable RG-316 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: SMA Male to RA SMC Plug Cable RG-316 Coax FMC0228315

URL: https://www.fairviewmicrowave.com/sma-male-ra-smc-plug-cable-rg316-coax-fmc0228315-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







FAIRVIEW MICROWAVE INC.	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
SMA Male to RA SMC Plug Cable RG-316 Coax	dwg no FI	MC0228315		CAGE CODE 3FKR5		
	CAD FILE 101614	SHEET	SCALE	E N/A	SIZE A	5568

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689