

FMC0717315LF **DATA SHEET**

MCX Plug to RA MCX Plug Cable RG-316 Coax with LF Solder

The MCX plug to RA MCX plug cable using RG-316 coax, part number FMC0717315LF, from Fairview Microwave is in-stock and ships same day. This Fairview MCX to MCX cable assembly has a plug to plug gender configuration with 50 ohm flexible RG-316 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC0717315LF MCX plug to MCX plug cable assembly operates to 3 GHz. The right angle MCX interface on the RG-316 cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Min | Т | ур | Max | ι | Jnits |
|-----|-------------|----|--------|----------------|----------------|
| DC | | | 3 | | GHz |
| | | | 1.35:1 | | |
| | 70 | | | % | |
| | 32 [104.99] | | pF/f | pF/ft [pF/m] | |
| | | DC | DC 70 | DC 3 1.35:1 70 | DC 3 1.35:1 70 |

Mechanical Specifications

Cable Assembly

Length*

Cable

Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields

Shield Layer 1 Jacket Material Jacket Diameter 0 in [0 mm]

RG-316 50 Ohms Stranded Copper, Silver PTFE

Silver Plated Copper Braid

FEP, Tan

0.098 in [2.49 mm]



Configuration:

- MCX Plua
- MCX Plug Right Angle
- RG-316

Features:

- Max Frequency 3 GHz
- 70% Phase Velocity
- FEP Jacket

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Connectors

| Description | Connector 1 | Connector 2 | | | |
|----------------------------|---------------------|-----------------|--|--|--|
| Туре | MCX Plug | MCX Plug | | | |
| Configuration | Straight | Right Angle | | | |
| Impedance | 50 Ohms | 50 Ohms | | | |
| Contact Material & Plating | Brass, Gold | Brass, Gold | | | |
| Contact Plating Spec. | 30μ" Min | 30μ in. minimum | | | |
| Dielectric Type | tric Type PTFE PTFE | | | | |
| Body Material & Plating | Brass, Gold | Brass, Gold | | | |
| Body Plating Spec. | 3μ" Minimum | 3μ in. minimum | | | |
| | | | | | |

Environmental Specifications

Temperature

Operating Range -55 to +125 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration: FMC0717315LF - xx

| cm = Centimeters | chank> = Inches

Length

Example: FMC0717315LF-12 = 12 inches long cable

FMC0717315LF-100cm = 100 cm long cable

MCX Plug to RA MCX Plug Cable RG-316 Coax with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: MCX Plug to RA MCX Plug Cable RG-316 Coax with LF Solder FMC0717315LF


URL: https://www.fairviewmicrowave.com/standard-mcx-plug-ra-mcx-plug-cable-rg316-coax-fmc0717315lf-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







| 1 - | FAIRVIEW MICROWAVE INC. LLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM | NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm]. | | | | | | |
|-----|--|---|--------|-------|------|-----------------|--------|------|
| '- | MCX Plug to RA MCX Plug Cable RG-316 Coax with LF Solder | FMC0717315LF | | | | CAGE CODE 3FKR5 | | |
| Sol | | CAD FILE | 102114 | SHEET | SCAL | E N/A | SIZE A | 5568 |