

# FMC0810315 DATA SHEET

## BNC Male to 10-32 Male Cable RG-316 Coax

The BNC male to 10-32 male cable using RG-316 coax, part number FMC0810315, from Fairview Microwave is in-stock and ships same day. This Fairview BNC to 10-32 cable assembly has a male to male gender configuration with 50 ohm flexible RG-316 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC0810315 BNC male to 10-32 male cable assembly operates to 2 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

## **Electrical Specifications**

| Description             | Min | Ty     | /р Мах | Units        |
|-------------------------|-----|--------|--------|--------------|
| Frequency Range         | DC  |        | 2      | GHz          |
| VSWR                    |     |        | 1.5:1  |              |
| Velocity of Propagation |     | 7      | 0      | %            |
| Capacitance             |     | 32 [10 | 04.99] | pF/ft [pF/m] |

### **Performance by Frequency**

| Description           | F1   | F2   | F3   | F4   | F5   | Units |
|-----------------------|------|------|------|------|------|-------|
| Frequency             | 0.05 | 0.1  | 0.25 | 0.5  | 2    | GHz   |
| Insertion Loss (Typ.) | 0.08 | 0.11 | 0.16 | 0.24 | 0.48 | dB/ft |
|                       | 0.26 | 0.36 | 0.52 | 0.79 | 1.57 | dB/m  |

## Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.2dB connector loss.

### **Mechanical Specifications**

### **Cable Assembly**

 Diameter
 0.571 in [14.5 mm]

 Weight
 0.03086 lbs [14 g]

### Cable

Cable Type

Jacket Material

Jacket Diameter

Impedance
Inner Conductor Type
Inner Conductor Material and Plating
Dielectric Type
Number of Shields
Shield Layer 1

RG-316 50 Ohms Solid Copper, Silver

PTFE 1

Silver Plated Copper Braid

FFP

0.098 in [2.49 mm]



## **Configuration:**

- BNC Male
- 10-32 Male
- RG-316

### **Features:**

- Max Frequency 2 GHz
- 70% Phase Velocity
- FEP Jacket

## **Applications:**

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





### **Connectors**

| Description                | Connector 1      | Connector 2   |  |  |
|----------------------------|------------------|---------------|--|--|
| Туре                       | BNC Male         | 10-32 Male    |  |  |
| Impedance                  | 50 Ohms          | 50 Ohms       |  |  |
| Contact Material & Plating | Brass, Gold      | Brass, Gold   |  |  |
| Contact Plating Spec.      | 50µ in. minimum  | MIL-G-45204   |  |  |
| Dielectric Type            | PTFE             | PTFE          |  |  |
| Body Material & Plating    | Brass, Nickel    | Brass, Nickel |  |  |
| Body Plating Spec.         | 100µ in. minimum |               |  |  |
|                            |                  |               |  |  |

## **Environmental Specifications**

**Temperature** 

Operating Range

-65 to +165 deg C


**Compliance Certifications** (see product page for current document)

### **Plotted and Other Data**

Notes:

#### **How to Order**

Part Number Configuration:



Example: FMC0810315-12 = 12 inches long cable

FMC0810315-100cm = 100 cm long cable

BNC Male to 10-32 Male Cable RG-316 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: BNC Male to 10-32 Male Cable RG-316 Coax FMC0810315

URL: https://www.fairviewmicrowave.com/bnc-male-10-32-male-cable-rg316-coax-fmc0810315-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2020

REV 1.0 Page 2 of 3





