

FMC0815240 DATA SHEET

BNC Male to 7/16 DIN Male Cable LMR-240 Coax

Electrical Specifications

Description		Min	Тур	Max	Units
Frequency Range		DC		2.5	GHz
VSWR				1.35:1	
Velocity of Propagation			84		%
RF Shielding		90			dB
Capacitance			24.2 [79.4]		pF/ft [pF/m]
Inductance			0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Cor	nductor		3.2 [10.5]		Ω/1000ft [Ω/Km]
DC Resistance Outer Co	nductor		3.89 [12.76]		$\Omega/1000$ ft [$\Omega/$ Km]



Configuration:

- BNC Male
- 7/16 DIN Male
- LMR-240

Mechanical Specifications

Cable Assembly

Weight 0.2134 lbs [96.8 g] Cable Cable Type LMR-240 **Impedance** 50 Ohms Inner Conductor Type Solid Inner Conductor Material and Plating Copper Dielectric Type PE (F) Number of Shields Shield Layer 1 **Tinned Copper** Shield Layer 2 Aluminum Tape Jacket Material PE, Black Jacket Diameter 0.24 in [6.1 mm]

Connectors

Description	Connector 1	Connector 2
Туре	BNC Male	7/16 DIN Male
Polarity	Standard	Standard
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Brass, Gold	Brass, Silver
Dielectric Type	PTFE	PTFE
Body Material & Plating	Brass, Tri-Metal	Brass, Tri-Metal

Environmental Specifications Temperature

Operating Range

-65 to +85 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013


Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





Typical Performance Data



Part Number Configuration:

cm = Centimeters

blank> = Inches Length

Example: FMC0815240-12 = 12 inches long cable

FMC0815240-100cm = 100 cm long cable

BNC Male to 7/16 DIN Male Cable LMR-240 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: BNC Male to 7/16 DIN Male Cable LMR-240 Coax FMC0815240

URL: https://www.fairviewmicrowave.com/bnc-male-7-16-male-cable-times-lmr-240-coax-fmc0815240-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
BNC Male to 7/16 DIN Male Cable LMR-240 Coax	DWG NO FMC0815240-XX			cage code 3FKR5		
	CAD FILE 102814	SHEET	SCALI	E N/A	SIZE A	5568