

# Low Loss BNC Male to 7/16 DIN Male Cable LMR-240 Coax with LF Solder

The BNC male to 7/16 DIN male cable using LMR-240 coax, part number FMC0815240LF, from Fairview Microwave is in-stock and ships same day. This Fairview BNC to 7/16 DIN cable assembly has a male to male gender configuration with 50 ohm flexible LMR-240 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC0815240LF BNC male to 7/16 DIN male cable assembly operates to 2.5 GHz. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

## **Electrical Specifications**

Description	Min	Т	Гур Max Ur		Inits	
Frequency Range	DC			2.5		GHz
VSWR				1.35:1		
Velocity of Propagation		8	34			%
RF Shielding	90					dB
Capacitance		24.2	[79.4]		pF/fl	[pF/m]
Inductance		0.06	[0.2]		uH/fl	[uH/m]
DC Resistance Inner Conductor		3.2 [10.5]		Ω/1000ft [Ω/Km]		
DC Resistance Outer Cor	nductor	3.89	[12.76]		Ω/100	0ft [Ω/Km]

## **Mechanical Specifications**

#### **Cable Assembly**

Length\*

Cable

Cable Type Impedance Inner Conductor Type

Inner Conductor Material and Plating

Dielectric Type Number of Shields

Shield Layer 1 Shield Layer 2 Jacket Material Jacket Diameter 0 in [0 mm]

LMR-240 50 Ohms Solid Copper PE (F)

Tinned Copper Aluminum Tape PE, Black

0.24 in [6.1 mm]

## FMC0815240LF DATA SHEET



## **Configuration:**

- BNC Male
- 7/16 DIN Male
- LMR-240


## **Features:**

- Max Frequency 2.5 GHz
- Shielding Effectivity > 90 dB
- 84% Phase Velocity
- Double Shielded
- PE Jacket

## **Applications:**

- General Purpose
- Laboratory Use

## **Cable Diagram:**



Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com

sales@fairviewmicrowave.com





Length

#### **Connectors**

Connector 1	Connector 2		
BNC Male	7/16 DIN Male		
50 Ohms	50 Ohms		
Brass, Gold	Brass, Silver		
PTFE	PTFE		
Brass, Tri-Metal	Brass, Tri-Metal		
	BNC Male 50 Ohms Brass, Gold PTFE		

**Environmental Specifications** 

**Temperature** 

Operating Range

-65 to +85 deg C

**Compliance Certifications** (see product page for current document)

Plotted and Other Data

Notes:

**How to Order** 

Example: FMC0815240LF-12 = 12 inches long cable FMC0815240LF-100cm = 100 cm long cable

Low Loss BNC Male to 7/16 DIN Male Cable LMR-240 Coax with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Low Loss BNC Male to 7/16 DIN Male Cable LMR-240 Coax with LF Solder FMC0815240LF


URL: https://www.fairviewmicrowave.com/standard-bnc-male-7-16-din-male-cable-lmr240-coax-fmc0815240lf-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES:  1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  3. DIMENSIONS ARE IN INCHES [mm].						
Low Loss BNC Male to 7/16 DIN Male Cable LMR-240	DWG NO FMC0815240LF			CAGE CODE 3FKR5			
Coax with LF Solder	CAD FILE 102814	SHEET	SCALE	N/A	SIZE A	5568	