

FMC0823240 DATA SHEET

BNC Male to RA QMA Male Cable LMR-240 Coax with Times Microwave Connectors

Electrical Specifications

| Description | | Min | Тур | Max | Units |
|-------------------------|---------|-----|--------------|--------|----------------------------------|
| Frequency Range | | DC | | 2.5 | GHz |
| VSWR | | | | 1.35:1 | |
| Velocity of Propagation | | | 84 | | % |
| RF Shielding | | 90 | | | dB |
| Capacitance | | | 24.2 [79.4] | | pF/ft [pF/m] |
| Inductance | | | 0.06 [0.2] | | uH/ft [uH/m] |
| DC Resistance Inner Cor | ductor | | 3.2 [10.5] | | Ω/1000ft [Ω/Km] |
| DC Resistance Outer Cor | nductor | | 3.89 [12.76] | | $\Omega/1000$ ft [$\Omega/$ Km] |



Configuration:

- BNC Male
- QMA Male Right Angle
- LMR-240

Mechanical Specifications

Cable Assembly

Weight 0.04982 lbs [22.6 g] Cable Cable Type LMR-240 **Impedance** 50 Ohms Inner Conductor Type Solid Inner Conductor Material and Plating Copper Dielectric Type PE (F) Number of Shields Shield Layer 1 **Tinned Copper** Shield Layer 2 Aluminum Tape Jacket Material PE, Black Jacket Diameter 0.24 in [6.1 mm]

Connectors

| Description | Connector 1 | Connector 2 | | | |
|-------------------------------|------------------|-----------------------|--|--|--|
| Туре | BNC Male | QMA Male | | | |
| Polarity | Standard | Standard | | | |
| Impedance | 50 Ohms | 50 Ohms | | | |
| Contact Material & Plating | Brass, Gold | Phosphor Bronze, Gold | | | |
| Dielectric Type | PTFE | PTFE | | | |
| Outer Cond Material & Plating | | Brass, Nickel | | | |
| Body Material & Plating | Brass, Tri-Metal | Brass, Nickel | | | |
| | | | | | |

Environmental Specifications

Temperature

Operating Range -65 to +85 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013


Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com






Typical Performance Data



How to Order



Example: FMC0823240-12 = 12 inches long cable FMC0823240-100cm = 100 cm long cable

BNC Male to RA QMA Male Cable LMR-240 Coax with Times Microwave Connectors from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: BNC Male to RA QMA Male Cable LMR-240 Coax with Times Microwave Connectors FMC0823240


URL: https://www.fairviewmicrowave.com/bnc-male-ra-qma-plug-cable-times-lmr-240-coax-fmc0823240-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







| FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM | NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm]. | | | | | |
|--|---|-------|-------|-----------------|--------|------|
| BNC Male to RA QMA Male Cable LMR-240 Coax with Times Microwave Connectors | DWG NO FMC0823240 | | | CAGE CODE 3FKR5 | | |
| | CAD FILE 102814 | SHEET | SCALI | E N/A | SIZE A | 5568 |