

SMA Female to RA MMCX Plug Cable RG-316 Coax

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		3	GHz
Velocity of Propagation	70			%
Capacitance	32 [104.99]			pF/ft [pF/m]

Mechanical Specifications

Cable Assembly				
Weight		0.00661 lbs [3 g]		
Cable Cable Type		RG-316		
Impedance		50 Ohms		
Inner Conductor Type		Stranded		
Inner Conductor Material and Plating		Copper, Silver		
Dielectric Type		PTFE		
Number of Shields		1		
Shield Layer 1		Silver Plated Copper Tape		
Shield Layer 2		Silver Plated Copper Braid		
Jacket Material		FEP, Tan		
Jacket Diameter		0.098 in [2.49 mm]		

Connectors

Description	Connector 1	Connector 2
Туре	SMA Female	MMCX Plug
Configuration	Straight	Right Angle
Polarity	Standard	Standard
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Beryllium Copper, Gold	Brass, Gold
Contact Plating Spec.	50µ in. minimum	
Dielectric Type	Teflon	Teflon
Hex Size	1/4 inch	
Body Material & Plating	Brass, Gold	Brass, Gold
Body Plating Spec.	3µ in. minimum	

Environmental Specifications

Temperature Operating Range

-65 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com

FMC1319315 DATA SHEET



Configuration:

- SMA Female
- MMCX Plug Right Angle
- RG-316



FMC1319315 DATA SHEET

Typical Performance Data - Spec VSWR 1.35:1 (RL= -16.5 dB) -10 .20 \$11 dB \$21 dE -30 -3 3.0 1.5 2.0 2.5 GH7 bly, FMC1319315-12 Typical data from a 12 inch cable as **How to Order** FMC1319315 - xx Part Number Configuration: uu cm = Centimeters <black> = Inches Length Example: FMC1319315-12 = 12 inches long cable FMC1319315-100cm = 100 cm long cable

SMA Female to RA MMCX Plug Cable RG-316 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: SMA Female to RA MMCX Plug Cable RG-316 Coax FMC1319315


URL: https://www.fairviewmicrowave.com/sma-female-ra-mmcx-male-cable-rg316-coax-fmc1319315-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







FAIRVIEW MICROWAVE INC.	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
SMA Female to RA MMCX Plug Cable RG-316 Coax	DWG NO FMC1319315			CAGE CODE 3FKR5		
	CAD FILE 103014	SHEET	SCALE N/A	SIZE A	5568	

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689