

FMC1719315 DATA SHEET

RA MCX Plug to RA MMCX Plug Cable RG316 Coax

The RA MCX plug to RA MMCX plug cable using RG-316 coax, part number FMC1719315, from Fairview Microwave is in-stock and ships same day. This Fairview MCX to MMCX cable assembly has a plug to plug gender configuration with 50 ohm flexible RG-316 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC1719315 MCX plug to MMCX plug cable assembly operates to 3 GHz. The right angle MCX and right angle MMCX interfaces on the RG-316 cable allow for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Т	ур	Max	ι	Jnits
Frequency Range	DC			3		GHz
VSWR				1.4:1		
Velocity of Propagation		70		%		
Capacitance		32 [104.99]			pF/f	t [pF/m]

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Typ.)	0.11	0.16	0.21	0.38	0.58	dB/ft
	0.36	0.52	0.69	1.25	1.9	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as $0.10dB \times SQRT(Frequency GHz)$ per connector.

Mechanical Specifications

Cable Assembly

Jacket Diameter

Weight 0.00529 lbs [2.4 g]

Cable

Cable Type
Impedance
Inner Conductor Type
Inner Conductor Material and Plating
Dielectric Type
Number of Shields
Shield Layer 1
Shield Layer 2
Jacket Material

RG-316 50 Ohms Solid Copper, Silver PTFE

Silver Plated Copper Tape Silver Plated Copper Braid FEP. Black

0.098 in [2.49 mm]



Configuration:

- MCX Plug Right Angle
- MMCX Plug Right Angle
- RG-316

Features:

- Max Frequency 3 GHz
- 70% Phase Velocity
- FEP Jacket

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056

Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com





Connectors

Description	Connector 1	Connector 2			
Туре	MCX Plug	MMCX Plug			
Impedance	50 Ohms	50 Ohms			
Contact Material & Plating	Brass, Gold	Brass, Gold			
Contact Plating Spec.	30μ in. minimum				
Dielectric Type	Teflon	Teflon			
Body Material & Plating	Brass, Gold	Brass, Gold			
Body Plating Spec.	3μ in. minimum				

Mechanical Specification Notes:

Environmental Specifications

Temperature

Operating Range

-55 to +125 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

FMC1719315 - xx uu

cm = Centimeters

chlank> = Inches

Length

Example: FMC1719315-12 = 12 inches long cable

FMC1719315-100cm = 100 cm long cable

RA MCX Plug to RA MMCX Plug Cable RG316 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: RA MCX Plug to RA MMCX Plug Cable RG316 Coax FMC1719315

URL: https://www.fairviewmicrowave.com/ra-mcx-male-ra-mmcx-male-cable-rg316-coax-fmc1719315-p.aspx


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

^{*}All cable assemblies have a length tolerance of 1.5% or ± 3/8", whichever is greater.







STANDARD TOLERANCES

.X ±0.2 .XX ±0.01 .XXX ±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
TITLE	DWG NO FMC1719315				CAGE CODE 3FKR5		
RA MCX Plug to RA MMCX Plug Cable RG316 Coax	CAD FILE 022018	SHEET 1 OF 1	SCAL	E N/A	SIZE A	7361	