

FMC2222085 **DATA SHEET**

SMP Female to SMP Female Cable FM-F086 Coax

Electrical Specifications

Description	Min	Тур	Max	Units				
Frequency Range	DC		18	GHz				
VSWR		1.35:1						
Velocity of Propagation		70.6		%				
Capacitance	28	3.95 [94.9	pF/ft [pF/m]					

Mechanical Specifications

Cable Assembly

Weight 0.00088 lbs [0.4 q]

Cable

Cable Type FM-F086 Impedance 50 Ohms Solid Inner Conductor Type Inner Conductor Material and Plating Copper, Silver

Dielectric Type PTFE

Number of Shields Shield Layer 1 Shield Layer 2 Jacket Material Jacket Diameter

Silver Plated Copper Tape Silver Plated Copper Braid

FEP, Blue

0.104 in [2.64 mm]



Configuration:

- SMP Female
- SMP Female
- FM-F086

Connectors

Description Connector 1		Connector 2			
Туре	SMP Female	SMP Female			
Polarity	Standard	Standard			
Impedance	50 Ohms	50 Ohms			
Contact Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold			
Contact Plating Spec.	30µ in. minimum	30µ in. minimum			
Dielectric Type	PTFE	PTFE			
Body Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold			
Body Plating Spec.	30µ in. minimum	30µ in. minimum			

Environmental Specifications Temperature

Operating Range

-65 to +165 deg C

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

Plotted and Other Data

Notes:

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

sales@fairviewmicrowave.com


Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com



dank> = Inches

Length

Typical Performance Data



Example: FMC2222085-12 = 12 inches long cable

FMC2222085-100cm = 100 cm long cable

SMP Female to SMP Female Cable FM-F086 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: SMP Female to SMP Female Cable FM-F086 Coax FMC2222085

URL: http://www.fairviewmicrowave.com/smp-female-smp-female-cable-hs086-coax-fmc2222085-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					NY TIME.
SMP Female to SMP Female Cable FM-F086 Coax	DWG NO FMC2222085			CAGE CODE 3FKR5		
	CAD FILE 103114	SHEET	SCALE	N/A	SIZE A	5568