

SMA Male to RA SSMB Plug Cable RG-188 Coax




FMCA100071

Configuration

- Connector 1: SMA Male
- Connector 2: SSMB Plug Right Angle
- Cable Type: RG-188
- Coax Flex Type: Flexible

Features

- PTFE Jacket



Applications

- General Purpose
- Laboratory Use

Description

The SMA male to RA SSMB plug cable using RG188 coax, part number FMCA100071, from Fairview Microwave is in-stock and ships same day. This Fairview SMA to SSMB cable assembly has a male to plug gender configuration with 50 ohm flexible RG-188 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The right angle SSMB interface on the RG-188 cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.028 lbs [12.7 g]

Cable

Cable Type	RG-188
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Silver Plated Copper Braid
Jacket Material	PTFE, White
Jacket Diameter	0.11 in [2.79 mm]

SMA Male to RA SSMB Plug Cable RG-188 Coax



FMCA100071

Connectors

Description	Connector 1	Connector 2
Type	SMA Male	SSMB Plug Right Angle
Specification	MIL-STD-348A	MIL-STD-348
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Right Angle
Contact Material and Plating	Brass, Gold	Gold
Contact Plating Specification	50 µin minimum	MIL-G-45204
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Gold	Brass, Gold
Body Plating Specification	3 µin minimum	MIL-G-45204
Coupling Nut Material and Plating	Brass, Gold	
Coupling Nut Plating Specification	3 µin minimum	

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

SMA Male to RA SSMB Plug Cable RG-188 Coax



FMCA100071

Typical Performance Data

How to Order

Part Number Configuration:

FMCA100071

- xx

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: FMCA100071-12 = 12 inches long cable
FMCA100071-100cm = 100 cm long cable

SMA Male to RA SSMB Plug Cable RG-188 Coax from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [SMA Male to RA SSMB Plug Cable RG-188 Coax FMCA100071](#)

URL: <https://www.fairviewmicrowave.com/sma-male-to-ra-ssmb-plug-cable-rg188-coax-fmca100071-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

