

# Water Blue FAKRA Jack to BNC Female Cable Using RG316 Coax

The FAKRA Code / Water Blue jack to BNC female cable using RG-316 coax, part number FMCA1342, from Fairview Microwave is in-stock and ships same day. This Fairview FAKRA to BNC cable assembly has a jack to female gender configuration with 50 ohm flexible RG316 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA1342 FAKRA jack to BNC female cable assembly operates to 1 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

## **Electrical Specifications**

Description	Min	Т	ур	Max	U	Inits
Frequency Range	DC			1,000		MHz
VSWR				1.4:1		
Capacitance		32 [1	04.99	]	pF/fl	: [pF/m]

Performance by Description	F1	F2	F3	F4	F5	Units
Frequency	50	100	250	500	1,000	MHz
Insertion Loss (Typ.)	0.275	0.31	0.36	0.438	0.58	dB/ft
	0.9	1.02	1.18	1.44	1.9	dB/m

## **Mechanical Specifications**

Cable Assembly
Diameter
Weight

#### Cable

Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Shield Layer 1 Jacket Material Jacket Diameter 0.453 in [11.51 mm] 0.021 lbs [9.53 g]

RG316 50 Ohms Stranded Copper Clad Steel, Silver PTFE 1 Silver Plated Copper Braid FEP, Tan 0.098 in [2.49 mm]



**FMCA1342** 

**DATA SHEET** 

# **Configuration:**

- FAKRA Jack
- BNC Female
- RG316

# **Features:**

- Max Frequency 1 GHz
- FEP Jacket

# **Applications:**

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com Fairview Microwave

an INFINIT ibrand



#### Connectors

Description	Connector 1	Connector 2 BNC Female Straight MIL-STD-348A 50 Ohms Brass, Gold 30µ in. minimum		
Туре	FAKRA Jack	BNC Female		
Configuration	Straight	Straight		
Specification		MIL-STD-348A		
Impedance	50 Ohms	50 Ohms		
Contact Material & Plating	Phosphor Bronze, Gold	Brass, Gold		
Contact Plating Spec.		30µ in. minimum		
Dielectric Type	Teflon	Teflon		
Outer Cond Material & Plating	Brass, Nickel			
Body Material & Plating	Plastic, Paint	Brass, Nickel		
Body Plating Spec.		100µ in. minimum		

#### Mechanical Specification Notes:

\*All cable assemblies have a length tolerance of 1.5% or  $\pm 3/8"$ , whichever is greater.

#### **Environmental Specifications**

**Temperature** Operating Range

-40 to +80 deg C

#### **Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**


Notes:

• Values at 25°C, sea level.

## How to Order

Part Number Configuration:

FMCA1342 - xx uu



Example: FMCA1342-12 = 12 inches long cable FMCA1342-100 cm = 100 cm long cable






Water Blue FAKRA Jack to BNC Female Cable Using RG316 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Water Blue FAKRA Jack to BNC Female Cable Using RG316 Coax FMCA1342

URL: https://www.fairviewmicrowave.com/fakra-jack-bnc-female-cable-rg316-coax-fmca1342-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave necessary to an take any representation or warraty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





Water Blue FAKRA Jack to BNC Female Cable Using RG316 Coax

NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].								
DWG NO FMCA1342				CAGE CODE 3FKR5				
CAD FILE	09/21/19	SHEET	1 OF 1	SCALE N/A		SIZE A	7361	

FMCA1342 DATA SHEET

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689