

# FMCA1560 DATA SHEET

# Slide-On BMA Jack Bulkhead to Slide-On BMA Jack Bulkhead Cable FM-SR086TBJ Coax

The BMA jack slide-on bulkhead to BMA jack slide-on bulkhead cable using FM-SR086TBJ coax, part number FMCA1560, from Fairview Microwave is in-stock and ships same day. This Fairview BMA to BMA cable assembly has a jack to jack gender configuration with 50 ohm formable FM-SR086TBJ coax. Fairview Microwave's formable RF cable assemblies provide an alternative to costly preformed semi-rigid assemblies since they are hand formable. The FMCA1560 BMA jack to BMA jack cable assembly operates to 18 GHz. Our RF cable assembly with BMA bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

# **Electrical Specifications**

-						
Description	Min	т	ур	Мах	ι	Inits
Frequency Range	DC			18		GHz
VSWR				1.5:1		
Return Loss				15.56		dB
Velocity of Propagation		6	9.5			%
RF Shielding	100					dB
Group Delay		1.43	[4.69]		ns/f	t [ns/m]
Capacitance		29 [9	95.14]		pF/f	t [pF/m]
DC Resistance Inner Cor	ductor	65.7 [	215.55	]	Ω/100	0ft [Ω/Km]
DC Resistance Outer Cor	nductor	10.2	[33.46]		Ω/100	0ft [Ω/Km]
Operating Voltage (AC)				350	١	/rms

## Performance by Frequency

Description	F1	F2	F3	F4	F5	Units	
Frequency	0.5	1	5	10	18	GHz	
Insertion Loss (Typ.)	0.15	0.23	0.55	0.81	1.13	dB/ft	
	0.49	0.75	1.8	2.66	3.71	dB/m	

#### Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

## **Mechanical Specifications**

Cable Assembly Diameter

0.37 in [9.4 mm]

Cable Cable Type

FM-SR086TBJ



# **Configuration:**

- Slide-On BMA Jack Bulkhead
- Slide-On BMA Jack Bulkhead
- FM-SR086TBJ

# **Features:**

- Max Frequency 18 GHz
- Shielding Effectivity > 100 dB
- 69.5% Phase Velocity
- FEP Jacket

# **Applications:**

- General Purpose
- Laboratory Use
- Rack and Panel
- BMA Cable RF Backplanes
- Phased Array Interconnects
- High Speed Switching Networks
- Blind Mate BMA Test

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com

REV 1.2 Page 1 of 5 Copyright © 2018





Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Outer Conductor Material and Plating Jacket Material Jacket Diameter 50 Ohms Solid Copper Clad Steel, Silver PTFE 1 Tinned Copper Composite Braid FEP, Black 0.105 in [2.67 mm]

One Time Minimum Bend Radius Repeated Minimum Bend Radius

0.5 in [12.7 mm] 0.787 in [19.99 mm]

### Connectors

Description	Connector 1	Connector 2		
Туре	BMA Jack	BMA Jack		
Mount Method	Bulkhead	Bulkhead		
Impedance	50 Ohms	50 Ohms		
Connection Method	Slide-On	Slide-On		
Contact Material & Plating	Beryllium Copper, G	old Beryllium Copper, Gold		
Outer Cond Material & Plat	ing Beryllium Copper, G	old Beryllium Copper, Gold		
Body Material & Plating	Brass, Tri-Metal	Brass, Tri-Metal		

Mechanical Specification Notes:

\*All cable assemblies have a length tolerance of 1.5% or  $\pm$  3/8", whichever is greater.

### **Environmental Specifications**

**Temperature** Operating Range

-55 to +105 deg C

Compliance Certifications (see product page for current document)


#### **Plotted and Other Data**

Notes:





## **Typical Performance Data**



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689






Slide-On BMA Jack Bulkhead to Slide-On BMA Jack Bulkhead Cable FM-SR086TBJ Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Slide-On BMA Jack Bulkhead to Slide-On BMA Jack Bulkhead Cable FM-SR086TBJ Coax FMCA1560


URL: https://www.fairviewmicrowave.com/bma-jack-bma-jack-cable-rg405-type-.086-coax-fmca1560-p.aspx



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







Slide-On BMA Jack Bulkhead to Slide-On BMA Jack Bulkhead Cable FM-SR086TBJ Coax

TITLE

3. DIMENSIONS ARE IN INCHES [mm].						
DWG NO			CAGE CODE			
FMCA15	50			3	FKR5	
CAD FILE 12/13/17	SHEET	SCAL	E N/A	SIZE A	CN2245	

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689