

FMCA1597 DATA SHEET

Slide-On BMA Plug Bulkhead to RA SMA Male Cable RG405 Type .086 Coax

The BMA plug slide-on bulkhead to RA SMA male cable using RG405 type .086 coax, part number FMCA1597, from Fairview Microwave is in-stock and ships same day. This Fairview BMA to SMA cable assembly has a plug to male gender configuration with 50 ohm semi-rigid FM-SR086CU coax. Fairview Microwave's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. The FMCA1597 BMA plug to SMA male cable assembly operates to 10 GHz. The right angle SMA interface on the FM-SR086CU cable allows for easier connections in tight spaces. Our RF cable assembly with BMA bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| • | | | | |
|-----------------|-----|----|--------|-------|
| Description | Min | Ту | /p Max | Units |
| Frequency Range | DC | | 10 | GHz |
| VSWR | | | 1.5:1 | |
| Return Loss | | | 15.56 | dB |

| Performance by | | | | | | |
|-----------------------|------|------|------|------|------|-------|
| Description | F1 | F2 | F3 | F4 | F5 | Units |
| Frequency | 0.5 | 1 | 2.5 | 5 | 10 | GHz |
| Insertion Loss (Typ.) | 0.15 | 0.22 | 0.32 | 0.49 | 0.8 | dB/ft |
| | 0.49 | 0.72 | 1.05 | 1.61 | 2.62 | dB/m |

Configuration:

- Slide-On BMA Plug Bulkhead
- SMA Male Right Angle
- FM-SR086CU

Features:

Max Frequency 10 GHz

Applications:

- General Purpose
- Laboratory Use
- Rack and Panel

- BMA Cable RF Backplanes
- Phased Array Interconnects
- High Speed Switching Networks
- Blind Mate BMA Test

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

| Cable Assembly | |
|----------------|-----------------|
| Diameter | 0.315 in [8 mm] |

Cable

Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating **Dielectric Type** Number of Shields Outer Conductor Material and Plating FM-SR086CU 50 Ohms Solid Copper Clad Steel, Silver PTFE 1 Copper

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com

REV 1.1 Page 1 of 5 Copyright © 2018





Repeated Minimum Bend Radius

0.05 in [1.27 mm]

Connectors

| Description | Connecte | or 1 | Connector 2 | | | |
|-----------------------------|------------------|--------|----------------------|-------------------------|--|--|
| Туре | BMA Plu | ıg | SMA Male | | | |
| Mount Method | Bulkhea | d | | | | |
| Impedance | 50 Ohm | าร | 50 Ohms | | | |
| Connection Method | Slide-O | n | | | | |
| Contact Material & Plating | Bronze, G | Gold | Brass, Gold over N | Brass, Gold over Nickel | | |
| Contact Plating Spec. | 51.18µ in. mi | nimum | 0.2 µin minimur | n | | |
| Dielectric Type | PTFE | | PTFE | | | |
| Outer Cond Material & Plat | ing Brass, Tri-N | /letal | | | | |
| Outer Cond Plating Spec. | 78.74µ in. mi | nimum | | | | |
| Body Material & Plating | Brass, Tri-N | 1etal | Brass, Gold over N | ickel | | |
| Body Plating Spec. | 78.74µ in. mi | nimum | 0.1 µin minimur | n | | |
| Coupling Nut Material & Pla | ating | | Passivated Stainless | Steel | | |
| Hex Size | 8 mm | | 5/16 inch | | | |
| Torque | | | 8 in-lbs [0.9 Nr | n] | | |
| | | | | - | | |

Mechanical Specification Notes:

*All cable assemblies have a length tolerance of 1.5% or $\pm 3/8"$, whichever is greater.

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:










Typical Performance Data



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689






Slide-On BMA Plug Bulkhead to RA SMA Male Cable RG405 Type .086 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Slide-On BMA Plug Bulkhead to RA SMA Male Cable RG405 Type .086 Coax FMCA1597


URL: https://www.fairviewmicrowave.com/bma-plug-ra-sma-male-cable-rg405-type-.086-coax-fmca1597-p.aspx



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







Slide-On BMA Plug Bulkhead to RA SMA Male Cable RG405 Type .086 Coax

| 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm]. | | | | | | |
|--|-------|------|-----------|--------|--------|--|
| DWG NO | | | CAGE CODE | | | |
| FMCA1597 | | | | 3 | FKR5 | |
| CAD FILE 12/19/17 | SHEET | SCAL | E N/A | SIZE A | CN2245 | |

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689