

FMCA3142 DATA SHEET

RA SHV Plug to RA SHV Plug Cable RG-58 Coax

The RA SHV plug to RA SHV plug cable using RG-58 coax, part number FMCA3142, from Fairview Microwave is in-stock and ships same day. This Fairview SHV to SHV cable assembly has a plug to plug gender configuration with 50 ohm flexible RG58 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA3142 SHV plug to SHV plug cable assembly operates to 300 MHz. The right angle SHV interfaces on the RG58 cable allow for easier connections in tight spaces. Safety high voltage connectors are designed to allow signal transmission with high voltage ratings without safety risk for the operators. Both the pin and socket contacts are securely recessed inside the insulation to guard against potential electrical shock when live unmated connectors are handled.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	T	ур	Max	Units
Frequency Range	DC			300	MHz
Velocity of Propagation		65	5.9		%
Capacitance		30.8 [L01.0!	5]	pF/ft [pF/m]
Operating Voltage (AC)				1,900	Vrms

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	50	100	250	300		MHz
Insertion Loss (Typ.)	0.029	0.049	0.074	0.082		dB/ft
	0.1	0.16	0.24	0.27		dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.2 dB per connector.

Mechanical Specifications

Cable Assembly

Length* 0 in [0 mm] Weight 0.126 lbs [57.15 g]

Cable

Cable Type RG58
Impedance 50 Ohms
Inner Conductor Type Stranded
Inner Conductor Material and Plating Copper, Tin
Dielectric Type PE
Number of Shields 1
Shield Layer 1 Tinned Copper Braid



Configuration:

- SHV Plug Right Angle
- SHV Plug Right Angle
- RG58

Features:

- Max Frequency 300 MHz
- 65.9% Phase Velocity
- PVC (NC) Jacket
- Dielectric withstanding of 5kV
- Shock, Moisture & Corrosion resistant
- Recessed contacts prevent shock hazards

Applications:

- General Purpose
- Laboratory Use
- Nuclear Instrumentation
- High Voltage Electrical Transmission
- Semiconductor Test

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Jacket MaterialPVC (NC), BlackJacket Diameter0.195 in [4.95 mm]

One Time Minimum Bend Radius 0.98 in [24.89 mm] Repeated Minimum Bend Radius 1.96 in [49.78 mm]

Connectors

Description	Connector 1		. Connector 2		
Туре	SHV Plug	SHV Plug S		g	
Specification	MIL-STD-34	MIL-STD-348B MIL-STD-		48B	
Impedance	50 Ohms	;	50 Ohms		
Contact Material & Plating	Brass, Gold over Nicke	l over c	copperBrass, Gold ov	er Nick	
Dielectric Type	Teflon		Teflon		
Body Material & Plating	Brass, Tinned C	Copper	Brass, Tinned (Copper	
Coupling Nut Material & Pla	iting Brass, Tinned C	Copper	Brass, Tinned (Copper	
Hex Size	7/16 Inch	ı	7/16 Inc	h	

Environmental Specifications

TemperatureOperating Range


-40 to +80 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

How to Order



RA SHV Plug to RA SHV Plug Cable RG-58 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: RA SHV Plug to RA SHV Plug Cable RG-58 Coax FMCA3142


URL: https://www.fairviewmicrowave.com/ra-shv-plug-to-ra-shv-plug-cable-rg58-coax-fmca3142-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







RA SHV Plug to RA SHV Plug Cable RG-58 Coax

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689