



RA SHV Plug to RA SHV Plug Cable RG188 Coax

The RA SHV plug to RA SHV plug cable using RG188 coax, part number FMCA3159, from Fairview Microwave is in-stock and ships same day. This Fairview SHV to SHV cable assembly has a plug to plug gender configuration with 50 ohm flexible RG188 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA3159 SHV plug to SHV plug cable assembly operates to 300 MHz. The right angle SHV interfaces on the RG188 cable allow for easier connections in tight spaces. Safety high voltage connectors are designed to allow signal transmission with high voltage ratings without safety risk for the operators. Both the pin and socket contacts are securely recessed inside the insulation to guard against potential electrical shock when live unmated connectors are handled.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	T	ур Мах	Units
Frequency Range	DC		300	MHz
Dielectric Withstanding Voltage (AC)			2,000	Vrms

Mechanical Specifications

Cable Assembly

Length* Weight

Cable

Cable Type Impedance

Inner Conductor Type

Inner Conductor Material and Plating

Dielectric Type
Number of Shields
Shield Layer 1
Jacket Material
Jacket Diameter

0 in [0 mm] 0.162 lbs [73.48 g]

RG188 50 Ohms Stranded

Copper Clad Steel, Silver PTFE

1

Silver Plated Copper Braid

PTFE, White

0.11 in [2.79 mm]



Configuration:

- SHV Plug Right Angle
- SHV Plug Right Angle
- RG188

Features:

- Max Frequency 300 MHz
- PTFE Jacket
- Dielectric withstanding of 5kV
- Shock, Moisture & Corrosion resistant
- Recessed contacts prevent shock hazards

Applications:

- General Purpose
- Laboratory Use
- Nuclear Instrumentation
- High Voltage Electrical Transmission
- Semiconductor Test

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Connectors

Description	Connector 1	Connector 2
Туре	SHV Plug	SHV Plug
Specification	MIL-STD-348B	MIL-STD-348B
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Brass, Tinned Copper	Brass, Tinned Copper
Dielectric Type	Teflon	Teflon
Body Material & Plating	Brass, Tinned Copper	Brass, Tinned Copper
Coupling Nut Material & Plating	Brass, Tinned Copper	Brass, Tinned Copper

Environmental Specifications

Temperature

Operating Range

-55 to +165 deg C


Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:



Example: FMCA3159-12 = 12 inches long cable

FMCA3159-100cm = 100 cm long cable

RA SHV Plug to RA SHV Plug Cable RG188 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and broadest selection in the industry.

Click the following link to obtain additional part information: RA SHV Plug to RA SHV Plug Cable RG188 Coax FMCA3159

URL: https://www.fairviewmicrowave.com/ra-shv-plug-to-ra-shv-plug-cable-rg188-coax-fmca3159-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.


301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2020

REV 1.0 Page 2 of 3







RA SHV Plug to RA SHV Plug Cable RG188 Coax

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689