

78 Ohm TRB 3-Slot Plug 1553 Connector Full Crimp Attachment for M17/176-00002



FMCN10-06031-206

Configuration

- · TRB 3-Slot Plug Connector
- MIL-STD-1553
- 78 Ohms

Features

- · Operating Frequency of 500 MHz Max.
- · Gold 30 micro inches Plated Beryllium Copper Contact
- · Contact plating according to ASTM-B-488

Applications

- · General Purpose Test
- · Custom Cable Assemblies
- · Robust Design

- Straight Body Geometry
- · Connector Interface Types: M17/176-00002
- Twinax Connectivity
- · Three lug bayonet coupling
- · Ease of use
- · Use in high shock and vibration environment

Description

78 Ohm TRB 3-Slot Plug Standard Connector Crimp/Crimp Attachment for M17/176-00002 Cable, part number FMCN10-06031-206, from Fairview Microwave is in-stock and ships same day. This TRB 3-Slot plug connector operates up to a maximum frequency of 500 MHz. These twinaxial cable plugs with TRB interface are the most popular cable plugs used in wide cable assembly applications to be used with Bus Couplers, avionics control boxes, Bus Relays, etc. This TRB plug has a bayonet coupling design with a center contact and an intermediate cylindrical contact. The bayonet type can withstand severe shocks and vibrations.

Fairview's 78 ohm TRB 3-Slot plug connector FMCN10-06031-206 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		500	MHz
Insertion Loss		0.1		dB
Impedance		78		Ohms

Mechanical Specifications

S	iz	E

CIEC	
Length	1.29 in [32.77 mm]
Width	0.57 in [14.48 mm]
Height	0.57 in [14.48 mm]
Weight	0.031 lbs [14.06 g]



78 Ohm TRB 3-Slot Plug 1553 Connector Full Crimp Attachment for M17/176-00002



FMCN10-06031-206

Material Specifications

Description	Material	Plating	
Contact	Beryllium Copper	Gold 30 micro inches	
		ASTM-B-488	
Insulation	Teflon		
Outer Conductor	Phosphor Bronze	ASTM-B-488	
Body	Brass	Nickel	
		ASTM-B-733	
Gasket	Rubber		
Crimp Sleeve	Brass	Nickel	

Environmental Specifications

Temperature

Operating Range

-55 to +200 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

78 Ohm TRB 3-Slot Plug 1553 Connector Full Crimp Attachment for M17/176-00002 from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 78 Ohm TRB 3-Slot Plug 1553 Connector Full Crimp Attachment for M17/176-00002 FMCN10-06031-206

URL: https://www.fairviewmicrowave.com/trb-3slot-plug-m17-176-00002-connector-fmcn10-06031-206-p.aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

