

78 Ohm TRB 3-Slot Plug 1553 Connector Full Crimp Attachment for Twinaxial OD .242" Cable



FMCN10-06031-210

Configuration

- TRB 3-Slot Plug Connector
- MIL-STD-1553
- 78 Ohms
- Straight Body Geometry
- Connector Interface Types: FMBC-30-02001, TWC-78-2, Belden 9272
- 1553 Design

Features

- Operating Frequency of 500 MHz Max.
- Gold 30 micro inches Plated Beryllium Copper Contact
- Contact plating according to ASTM-B-488
- Twinax Connectivity
- 3 Slot Bayonet Coupling

Applications

- General Purpose Test
- Robust Design
- Ease of Use
- Use in High Shock and Vibration Environment

Description

78 Ohm TRB 3-Slot Plug 1553 Connector Crimp/Crimp Attachment for FMBC-30-02001, TWC-78-2 and Belden 9272 Cable, part number FMCN10-06031-210, from Fairview Microwave is in-stock and ships same day. This TRB 3-Slot plug connector operates up to a maximum frequency of 500 MHz. These twinaxial cable plugs with TRB interface are the most popular cable plugs used in wide cable assembly applications to be used with Bus Couplers, avionics control boxes, Bus Relays, etc. This TRB plug has a bayonet coupling design with a center contact and an intermediate cylindrical contact. The bayonet type can withstand severe shocks and vibrations.

Fairview's 78 ohm TRB 3-Slot plug connector FMCN10-06031-210 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		500	MHz
Insertion Loss		0.1		dB
Impedance		78		Ohms

Mechanical Specifications

Size

Length	1.29 in [32.77 mm]
Width	0.57 in [14.48 mm]
Height	0.57 in [14.48 mm]
Weight	0.055 lbs [24.95 g]

78 Ohm TRB 3-Slot Plug 1553 Connector Full Crimp Attachment for Twinaxial OD .242" Cable



FMCN10-06031-210

Material Specifications

Description	Material	Plating
Contact	Beryllium Copper	Gold 30 micro inches ASTM-B-488
Insulation	Teflon	
Outer Conductor	Phosphor Bronze	ASTM-B-488
Body	Brass	Nickel ASTM-B-733
Gasket	Rubber	
Crimp Sleeve	Brass	Nickel

Environmental Specifications

Temperature Operating Range	-55 to 200 deg C
---------------------------------------	------------------

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

78 Ohm TRB 3-Slot Plug 1553 Connector Full Crimp Attachment for Twinaxial OD .242" Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: [78 Ohm TRB 3-Slot Plug 1553 Connector Full Crimp Attachment for Twinaxial OD .242" Cable FMCN10-06031-210](#)

URL: <https://www.fairviewmicrowave.com/trb-3-slot-plug-fmbc-30-02001-twc-78-2-belden-9272-connector-fmcn10-06031-210-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCN10-06031-210 CAD Drawing

78 Ohm TRB 3-Slot Plug 1553 Connector Full Crimp Attachment for Twinaxial OD .242" Cable



REVISION		DATE	CHANGED BY	APPROVED
ZONE	REV	DESCRIPTION		
	C	ECO-13202	KGLEBOVA	KHIETPAS

 Fairview Microwave an INFINIT® brand Website: www.FairviewMicrowave.com Phone: 1.800.715.4396 1.972.649.6678		 INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5 SCALE NONE SHEET 1 OF 2
DESCRIPTION 78 OHM TRB 3-SLOT PLUG 1553 CONNECTOR FULL CRIMP ATTACHMENT FOR TWINAXIAL OD .242" CABLE		
SIZE	CAGE CODE	DRAWN BY
A	3FKR5	SREITER
ITEM NO.	FMCN10-06031-210	
REV	C	

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN PAREMILLIMETERS

TOLERANCES:
 .X = ±.2 [5] FRACTIONS ±.1/32
 .XX = ±.02 [0.5] ANGLES ± 1°
 .XXX = ±.005 [0.13]

CABLE LENGTH TOLERANCES:
 >12 [305] ≤ 60 [1524] = +.1 [25] / -0
 >60 [1524] ≤ 120 [3048] = +.4 [102] / -0
 >120 [3048] ≤ 300 [7620] = +.8 [203] / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY. DIMENSIONS OF CRITICAL FEATURES UNLESS OTHERWISE SPECIFIED MAY VARY IN SIZE AND LOCATION. COLORS MAY VARY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

FW DS Rev-D4 A82P