



BMA Plug Bulkhead Slide-On Connector Solder/Non-Solder Contact Attachment For RG405, .086 SR Cable Gold Plated

BMA plug slide-on bulkhead connector with solder/non-solder contact attachment for RG405 and .086 SR, part number FMCN1195, from Fairview Microwave is instock and ships same day. This BMA plug connector operates up to a maximum frequency of 22 GHz and offers good VSWR of 1.3:1. This blind mate connector is ideal for applications without direct visual or tactile access to the connection point, for example, when two circuit boards need to be mated. Fairview's FMCN1195 bulkhead BMA connector enables designers to make external connections on product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Fairview's BMA plug bulkhead connector FMCN1195 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Min	Тур	Max	Units
DC		22	GHz
		1.3:1	
		0.14	dB
		350	Vrms
		1,000	Vrms
5,000			MOhms
	DC	DC	DC 22 1.3:1 0.14 350 1,000

Mechanical Specifications

 Size

 Length
 0.7 in [17.78 mm]

 Width/Dia.
 0.43 in [10.92 mm]

 Weight
 0.011 lbs [4.99 g]

 Mating Cycles
 1,000 Cycles

Material Specifications

Description	Material	Plating		
Contact	Beryllium Copper	Gold 51.18µ in. minimum		
Insulation	PTFE			
Outer Conductor	Stainless Steel	Gold 19.68µ in. minimum		
Body	Stainless Steel	Gold 19.68µ in. minimum		
Washer	Brass	Nickel		



Configuration:

- Slide-On BMA Plug Connector
- 50 Ohms
- Straight Body Geometry
- RG405, .086 SR Interface Type
- Solder/Non-Solder Contact Attachment
- Bulkhead
- 11 mm Hex

Features:

- Operating Frequency of 22 GHz Max.
- Good VSWR of 1.3:1
- · Blind Mate Connector
- Gold Plated Beryllium Copper Contact
- 51.18µ in. minimum contact plating
- Low-Engagement Force

Applications:

- General Purpose Test
- Rack and Panel Mount Applications
- Custom Cable Assemblies
- RF Backplanes
- Test I/O
- Blind Mating
- · Rack and Panel
- Phased Array Systems

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





O-Ring	Silicone Rubber

Environmental Specifications Temperature

Operating Range -65 to +125 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

BMA Plug Bulkhead Slide-On Connector Solder/Non-Solder Contact Attachment For RG405, .086 SR Cable Gold Plated from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: BMA Plug Bulkhead Slide-On Connector Solder/Non-Solder Contact Attachment For RG405, .086 SR Cable Gold Plated FMCN1195


URL: https://www.fairviewmicrowave.com/bma-plug-slide-on-rg405-.086-sr-connector-fmcn1195-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







ASSEMBLY PROCEDURES

- 1. STRIP CABLE AS SHOWN. DO NOT NICK CENTER CONDUCTOR.
- 2. SLIDE CABLE INTO CONNECTOR INSURING CENTER CONDUCTOR MATES WITH CENTER PIN.
- 3. OUTER CONDUCTOR BOTTOMS OUT WITH BODY SHOULDER. SOLDER OUTER CONDUCTOR TO BODY.

STA	NDARD	TOLERANCES
.X	±0.2	
.XX	±0.1	

XX ±0.1 XXX ±0.05

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
BMA Plug Bulkhead Slide-On Connector Solder/Non-Solder Contact Attachment For RG405, .086 SR Cable Gold Plated	DWG NO FMCN1195			CAGE CODE 3FKR5		
	CAD FILE 022117	SHEET	SCALE	≣ N/A	SIZE A	2233