



BMA Jack Bulkhead Slide-On Connector Solder Attachment For RG405, .086 SR, RG405 Tinned Cable

BMA jack slide-on bulkhead connector with solder/solder attachment for RG405, .086 SR and RG405 Tinned, part number FMCN1208, from Fairview Microwave is in-stock and ships same day. This BMA jack connector operates up to a maximum frequency of 18 GHz and offers excellent VSWR of 1.23:1. This blind mate connector is ideal for applications without direct visual or tactile access to the connection point, for example, when two circuit boards need to be mated. Fairview's FMCN1208 bulkhead BMA connector enables designers to make external connections on product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Fairview's BMA jack bulkhead connector FMCN1208 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		18	GHz
VSWR			1.23:1	
Insertion Loss			0.12	dB
Operating Voltage (AC)			350	Vrms
DWV (AC)			1,000	Vrms
Insulation Resistance	5,000			MOhms

Mechanical Specifications

 Size
 0.7 in [17.78 mm]

 Length
 0.37 in [9.40 mm]

 Weight
 0.0145 lbs [6.58 g]

 Mating Cycles
 1,000 Cycles

Material Specifications

Description	Material	Plating		
Contact	Beryllium Copper	Gold		
Outer Conductor	Beryllium Copper	Gold		
Body	Brass	Tri-Metal		
Washer	Brass Tri-Metal			

Mechanical Specification Notes:

Recommended axial float mount for best electricl performance: 0.51 + -0.25 mm (.020'' + -0.010)



Configuration:

- · Slide-On BMA Jack Connector
- 50 Ohms
- · Straight Body Geometry
- RG405, .086 SR, RG405 Tinned Interface Type
- Solder/Solder Attachment
- Bulkhead

Features:

- Operating Frequency of 18 GHz Max.
- Excellent VSWR of 1.23:1
- · Blind Mate Connector
- Gold Plated Beryllium Copper Contact
- IP54(Mated)
- Low-Engagement Force
- · Radial and Axial Float Versions

Applications:

- General Purpose Test
- Rack and Panel Mount Applications
- Custom Cable Assemblies
- · Phased Array Systems
- Blind Mating
- RF Backplanes
- Rack and Panel
- · Base Stations
- Test I/O

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Environmental Specifications Temperature

Operating Range Ingress Protection (IP) Rating -65 to +105 deg C IP54(Mated)

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

BMA Jack Bulkhead Slide-On Connector Solder Attachment For RG405, .086 SR, RG405 Tinned Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: BMA Jack Bulkhead Slide-On Connector Solder Attachment For RG405, .086 SR, RG405 Tinned Cable FMCN1208


URL: https://www.fairviewmicrowave.com/bma-jack-slide-on-rg405-.086-sr-rg405-tinned-connector-fmcn1208-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







ASSEMBLY PROCEDURES

- 1. STRIP CABLE AS SHOWN. DO NOT NICK CENTER CONDUCTOR.
- 2. SLIDE CABLE INTO CONNECTOR INSURING CENTER CONDUCTOR MATES WITH CENTER PIN.
- 3. OUTER CONDUCTOR BOTTOMS OUT WITH BODY SHOULDER. SOLDER OUTER CONDUCTOR TO BODY.

STANDARD TOLERANCES					
.X ±0.2					
.XX ±0.1					
.XXX ±0.05					

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

	FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
	MA Jack Bulkhead Slide-On Connector Solder attachment For RG405, .086 SR, RG405 Tinned Cable	DWG NO FMCN1208			CAGE CODE 3FKR5		
		CAD FILE	040417	SHEET	SCAL	E N/A	SIZE A